

Han-Eco 24B-HTE-for DL-M40



Part number	19 43 024 0428
Specification	Han-Eco 24B-HTE-for DL-M40
HARTING eCatalogue	https://b2b.harting.com/19430240428

Identification

Category	Hoods/Housings	
Series of hoods/housings Han-Eco [®] B		
Type of hood/housing	Hoods	

Version

Locking type	Double locking lever
Size	24 B
Version	Top entry
Cable entry	1x M40

Technical characteristics

Limiting temperature	-40 +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66

Material properties

Material (hood/housing)	Polyamide Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	IEC 61984
	EN 45545-2 R22: HL1, HL2, HL3
	EN 45545-2 R23: HL1, HL2, HL3
	EN 45545-2 R24: HL1, HL2, HL3

Commercial data

Packaging size	1
Country of origin	Germany

Product data sheet 19 43 024 0428 Han-Eco 24B-HTE-for DL-M40



Commercial data

European customs tariff number 85389099