


Fan Coil Filters



Advantages

- Light and robust
- Wide variety of sizes to meet your demands
- Ultra compact size
- reversible filter

Application: Prevention of dust and dirt build up on heating/cooling coils within ventilation systems

Type: Coarse dust removal

Frame: Metal with downstream support

Media: Polyester fiber

EN779:2012 efficiency: G3

Temperature: 70°C maximum in continuous service

Nota:

- packaging (10 pieces) for shipping

- G4 possible or impregnated carbon for odors



Article Number	Type	Filter class	Size (WxH) mm	Airflow/dP nominal m ³ /h/Pa	Media area m ²	Unit Volume m ³	Unit weight kg
1062.51.13	Fan Coil	G3	185x444	570/25	0,08	0,2	0,08
1062.51.14	Fan Coil	G3	185x594	770/25	0,11	0,3	0,11
1062.51.15	Fan Coil	G3	185x794	1030/25	0,15	0,4	0,15
1062.51.16	Fan Coil	G3	185x994	1280/25	0,18	0,5	0,18
1062.51.17	Fan Coil	G3	185x1194	1560/25	0,22	0,6	0,22
1062.51.21	Fan Coil	G3	174x650	790/25	0,11	0,3	0,11
1062.51.22	Fan Coil	G3	174x850	1040/25	0,15	0,4	0,15
1062.51.23	Fan Coil	G3	174x1050	1274/25	0,18	0,5	0,18
1062.51.24	Fan Coil	G3	174x1250	1520/25	0,22	0,6	0,22
1062.51.26	Fan Coil	G3	245x480	800/25	0,12	0,3	0,12
1062.51.27	Fan Coil	G3	245x730	1280/25	0,18	0,5	0,18
1062.51.28	Fan Coil	G3	245x1030	1760/25	0,25	0,7	0,25
1062.51.34	Fan Coil	G3	212x465	690/25	0,10	0,3	0,1
1062.51.35	Fan Coil	G3	212x665	990/25	0,14	0,4	0,14
1062.51.36	Fan Coil	G3	212x865	1280/25	0,18	0,5	0,18
1062.51.37	Fan Coil	G3	212x1065	1580/25	0,23	0,6	0,23
1062.51.46	Fan Coil	G3	205x660	990/25	0,14	0,4	0,14
1062.51.47	Fan Coil	G3	205x845	1200/20	0,17	0,5	0,18
1062.51.54	Fan Coil	G3	418x170	495/25	0,07	0,2	0,07
1062.01.93	Fan Coil	G3	578x208	850/25	0,12	0,3	0,12
1062.51.55	Fan Coil	G3	578x170	700/25	0,10	0,3	0,10
1062.51.56	Fan Coil	G3	778x170	990/25	0,14	0,4	0,14
1062.01.94	Fan Coil	G3	978x208	1500/25	0,21	0,6	0,21
1062.51.57	Fan Coil	G3	978x170	1200/25	0,17	0,5	0,17
1062.99.**	Fan Coil		custom made *				