

Needle power stripper



Technical characteristics

Max operating pressure: 6,2 bar

Applications: Stripping

Connection: Supplied with 3 adaptors: ISO 6150 B; European 7,4 mm; ARO 210

Needles Ø 3mm, length 180 mm

	A (mm)	B (mm)	Consumption (l/min)	Impact rate (bpm)	Piston stroke (mm)	BSPT female thread	Sound level (dB(A))	Weight (kg)	Parts Numbers
	290	185	85	3700	33	R 1/4	109	2.7	TSP 0333700

