

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [2153461111](#)  
**Status:** **Active**  
**Overview:** Off-the-Shelf Pre-Crimped Leads  
**Description:** Pre-Crimped Lead Squba 3.6 Female-to-Pigtail, Tin (Sn) Plating, 75.00mm Length, 18 AWG, Black

**Documents:**  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Datasheet \(PDF\)](#)

|                              |                                        |
|------------------------------|----------------------------------------|
| <b>General</b>               |                                        |
| Product Family               | Cable Assemblies                       |
| Series                       | <a href="#">215346</a>                 |
| Assembly Configuration       | Pre-crimped Lead Only                  |
| Connector to Connector       | Squba-to-Pigtail                       |
| Overview                     | <u>Off-the-Shelf Pre-Crimped Leads</u> |
| Product Name                 | Squba                                  |
| UPC                          | 195842349469                           |
| <b>Physical</b>              |                                        |
| Cable Length                 | 75.00mm                                |
| Circuits (Loaded)            | 1                                      |
| Color - Resin                | Black                                  |
| Gender                       | Female-Pigtail                         |
| Lock to Mating Part          | Yes                                    |
| Material - Metal             | Copper Alloy                           |
| Material - Plating Mating    | Matte Tin                              |
| Material - Resin             | Modified Polystyrene                   |
| Net Weight                   | 1.021/g                                |
| Number of Rows               | 1                                      |
| Packaging Type               | Bag                                    |
| Pitch - Mating Interface     | 3.60mm                                 |
| Plating min - Mating         | 2.540µm                                |
| Single Ended                 | Yes                                    |
| Termination Interface: Style | Crimp or Compression                   |
| Wire Insulation Diameter     | 1.90mm-2.40mm                          |
| Wire Size AWG                | 18                                     |
| Wire/Cable Type              | UL 11028                               |

|                               |       |
|-------------------------------|-------|
| <b>Electrical</b>             |       |
| Current - Maximum per Contact | 11.5A |
| Voltage - Maximum             | 600V  |

**Material Info**

|                                    |                |
|------------------------------------|----------------|
| <b>Reference - Drawing Numbers</b> |                |
| Sales Drawing                      | 2153461111-000 |



|                                                                                                                                                                                                                                                  |                                                                                               |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------|
| <b>EU ELV</b><br><b>Not Relevant</b>                                                                                                                                                                                                             |                                                                                               |
| <b>EU RoHS</b><br><b>Compliant</b><br><b>REACH SVHC</b><br>Not Contained Per -<br>D(2021)4569-DC (8<br>July 2021)<br><b>Halogen-Free</b><br><b>Status</b><br><b>Low-Halogen</b><br>For more information, please visit <a href="#">Contact US</a> | <b>China RoHS</b><br><br><br><br><br><br><br><br><br><br>China ROHS<br>ELV<br>RoHS Phthalates |
| Green Image<br>Not Relevant<br>Not Contained                                                                                                                                                                                                     |                                                                                               |

**Search Parts in this Series**  
[215346](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION