




Pushing Performance

## PCB receptacle fem. L-cod(60pcs) w/o FE



Part number	21 03 396 2506
Specification	PCB receptacle fem. L-cod(60pcs) w/o FE
HARTING eCatalogue	<a href="https://b2b.harting.com/21033962506">https://b2b.harting.com/21033962506</a>

### Identification

Category	Connector
Series	Circular connectors M12
Identification	M12 Power
Element	PCB adapter
Specification	Straight

### Version

Termination method	Reflow soldering termination (THR)
Gender	Female
Shielding	Shielded
Number of contacts	4
Coding	L-coding
Details	Order housings separately
Pack contents	Packaging: 60 pieces in a tray

### Technical characteristics

Rated current	16 A
Rated voltage	63 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Insulation resistance	$> 10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Ambient temperature	-40 ... +85 °C
Mating cycles	$\geq 100$



Pushing Performance

## Technical characteristics

Overvoltage category	III
Isolation group	I ( $600 \leq CTI$ )

## Material properties

Material (insert)	PA
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Gold plated

## Specifications and approvals

Specifications	IEC 61076-2-111
----------------	-----------------

## Commercial data

Packaging size	1
Net weight	12.43 g
Country of origin	Romania
European customs tariff number	85366990
eCl@ss	27440402 PCB connector