

Panel cut-out 16.2 mm / 22.5 mm

	Ø 18 IP40 exposed plastic bezel		Ø 18 IP40 concealed plastic bezel	Ø 18 IP67 exposed plastic bezel	Ø 25 IP65 plastic bezel	Ø 25 IP40 / IP65 aluminium bezel ★	Ø 25 IP65 aluminium bezel with sealing ring ★	
Contact blocks must be ordered separately (see pages 20 + 21)								
<b>Faston terminal</b> Momentary Latching ☺ Indicator	505 008 515 008 555 008	505 002 515 002 555 002	505 015 515 015 555 015	505 020 515 020 555 020	505 018 515 018 555 018	505 033 515 033 555 033		
<b>Solder terminal</b> Momentary Latching ☺ Indicator	505 108 515 108 555 108	505 102 515 102 555 102	505 115 515 115 555 115	505 120 515 120 555 120	505 118 515 118 555 118	505 133 515 133 555 133		
Weight in g	6		6	7	13	14	14	
Length in mm Switches Indicators	43 41		43 41	43 41	40 38	42 40	42 40	
Front panel thickness max. min.	6.5 1.0		6.5 1.0	6.5 1.0	5 1.0	5 1.0	5 1.0	
Bezel and lens heights (switch in „off“ position)								
<b>Lenses</b>	Ø 15 flat   concave		Ø 18	Ø 15	Ø 21	Ø 18 IP40   IP65		
Weight in g	0.7	0.8	0.9	0.8	0.8	0.9	1.1	
<b>opaque</b>	white yellow green blue red black orange	464 021 464 121 464 221 464 321 464 421 464 521 464 621	464 022 464 122 464 222 464 322 464 422 464 522 464 622	464 015 464 115 464 215 464 315 464 415 464 515 464 615	564 011 564 111 564 211 564 311 564 411 564 511 564 611	564 024 564 124 564 224 564 324 564 424 564 524 564 624	464 015 464 115 464 215 464 315 464 415 464 515 464 615	464 001 464 101 464 201 464 301 464 401 464 501 464 601
<b>transparent</b>	white yellow green blue red orange	465 021 465 121 465 221 465 321 465 421 465 621	465 022 465 122 465 222 465 322 465 422 465 622	465 015 465 115 465 215 465 315 465 415 465 615	565 011 565 111 565 211 565 311 565 411 565 611	565 024 565 124 565 224 565 324 565 424 565 624	465 015 465 115 465 215 465 315 465 415 465 615	465 001 465 101 465 201 465 301 465 401 465 601
★ Part number suffix for black anodized aluminium alloy ... .. 500, for transparent lens lower part ... .. 010 (except IP67 and Ø 21 IP65)								