



35HD Series Locking Plug

3.5mm plug with one piece tip rod for ultra-reliability. Locking collar secures plug to threaded bushing with M6 x 0.5 thread. Handle available with either .250 or .175 cable opening, heavy duty large cable clamp available. •Available in bulk or individually bagged (add PKG to the part number for individual bagging)

Specifications

- **Contact Resistance:** 20 MilliOhms Max.
- **Dielectric Withstanding Voltage:** 250 VAC Min.
- **Insulation Resistance @ 500 VDC:** 2,000 MegaOhms Min.
- **Max. Working Voltage:** 250 VAC; 140VDC
- **Current Carry @ Working Voltage:** 4 Amps
- **Insertion/Withdrawal Force:** Typical 2.5/2 Lbs.
- **Temperature Range:** -20°C to 85°C (operating)
- **Thermal Shock:** MIL-STD-202, Method 107G
- **Vibration:** MIL-STD-202, Method 201
- **Life:** 5,000 Cycles
- **Cable Size:** .250 Dia. Max.