

SPECIFICATION




Current Rate:1.5 AMP
Insulation Resistance:1000M Ω Min.
Contact Resistance:20m Ω Max.
Dielectric Voltage:500V AC for one minute
Operation Temperature:-40°C to +105°C

MATERIAL

Insulator:Polyester,UL 94V-0
Standard:Nylon 6T
Contact Pin:Copper Alloy
Contact Plating:Gold Flash all over

PBS1.27-x

Female Header 1.27mm 1 Row H=3.4/4.4mm Straight Type



Recommended PCB Layout
(PCB TOLERANCE ± 0.05)

