





REV	MODIFICATION	DATE	DRAW	APPROVE



SPECIFICATIONS:
 Current Rating: PIN Number-A 20A; PIN Number-B 12A; Number-C 5A;
 Operating Voltage: 500V MAX.
 Voltate Rating: 2500V MAX.
 Contact Resistance: 5.0mΩ MAX.
 Cable OD: ø4.0-ø11.5mm
 Waterproof Standard: IP67

2	Contact	Phosphor bronze	Gold Ptd.	2-12
1	Housing	PBT		5
No.	Description	Material	Treat	Q'ty

TYPE	PIN NUMBER-A			PIN NUMBER-B			PIN NUMBER-C	
P/N:	0262 02	0262 03	0262 04	0262 05	0262 07	0262 09	0262 12	
Female Contact Face View								
Number Of Contact	2	3	4	5	7	9	12	

-TOLERANCES- UNLESS OTHERWISE SPECIFIED		Lumberg passion for connections	
X.X ±0.25	X* REF ± 5*	TITLE: LP20 Serie 262 Female Connector All Plastic	
X.XX ±0.15	X.* ± 3*		
X.XXX±0.05	X** ± 1*		
DRAWN	ROBIN	02/01/2018	PRODUCT NO. ---
CHECKED			FILE NAME: ---
APPROVED			
SCALE: AS SHOWN	UNIT: mm	PORJ.	SIZE A4 REV. A SHEET. A/A