



2 X 5
STYLE A



2 X 5
STYLE B



2 X 7
STYLE C



2 X 8 THUR
STYLE D

KEY FOR PLATING AND TAIL LENGTH AND TYPE			
X	TERMINAL PLATING < NOTE 10 >	DIM S	TERMINAL TYPE
-0XX(LF)	30u" / .76u Au OVER 50u" / 1.27u Ni	.105/2.67	RD
-1XX(LF)	30u" / .76 GXT GOLD FLASH	.105/2.67	RD
-2XX(LF)	30u" / .76u Au OVER 50u" / 1.27u Ni	.150/3.81	RD
-3XX(LF)	30u" / .76 GXT GOLD FLASH	.150/3.81	RD
-4XX(LF)	30u" / .76u Au OVER 50u" / 1.27u Ni	.105/2.67	SQ
-5XX(LF)	30u" / .76 GXT GOLD FLASH	.105/2.67	SQ
-6XX(LF)	30u" / .76u Au OVER 50u" / 1.27u Ni	.150/3.81	SQ
-7XX(LF)	30u" / .76 GXT GOLD FLASH	.150/3.81	SQ
-8XX(LF)	15u" / .38u Au OVER 50u" / 1.27u Ni	.150/3.81	SQ
-9XX(LF)	15u" / .38u Au OVER 50u" / 1.27u Ni	.105/2.67	SQ

NOTES

- SAME PIN POSITION TOLERANCE APPLIES TO BOTH ENDS OF EACH TERMINAL.
- MOLDING MAT'L: 30% GLASS-FILLED POLYESTER, FLAME RETARDANT PER UL 94-V0, COLOR: BLUE.
- 1* MAX DRAFT PERMISSIBLE ON ALL SURFACES.
- 1.8 KILOGRAMS/4 POUNDS MIN. TERM. PULL-OUT FORCE.
- TERMINAL MAT'L: PHOSPHOR BRONZE.
- PART NUMBERS HAVING AN 'R' FOLLOWING THE 8 DIGIT P/N (EXAMPLE 69155-010 R) HAVE A RETENTION FEATURE. LOCATION IS MANUFACTURER'S OPTION.
- CONNECTORS WITH RETENTION AND ROUND PINS HAVE 15LB/6.8KG MAX INSERTION AND 25LB/11KG MIN RETENTION FORCE WHEN USED IN A .040/1.02±.003/.08 DIA HOLE AND A .062/1.58 THICK PCB BOARD.
- CONNECTORS WITH RETENTION AND SQUARE PINS HAVE A 15LB/6.8KG MAX INSERTION AND A 5LB/23KG MIN RETENTION WHEN USED IN A .040/1.02±.003/.08 DIA HOLE AND A .062/1.58 THICK PCB BOARD.
- DIMENSION 'A' FOR -034 HAS A MAXIMUM SIZE DF 1.990/50.6
- 69155-***LF IS JUST A LEAD FREE PRODUCT.
- THE HOUSING DF XXXX-XYLF WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER PROCESS.
- PLATING OPTION MAYBE EITHER GOLD OR GXT
- PLATING AT MANUFACTURER'S OPTION
- FOR 69155-150LF , THE TOLERANCE DF DIM ' S ' IS ' -0.10 , +0.35 ' .

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCI	
ltr	ecn no	dr	date	linear	projection	title	www.fciconnect.com
M				.XX±.01 / .X±.3	projection	HEADER QUICKIE SLIM LINE RIGHT ANGLE 4 WALL	
				.XXX±.005 / .XX±.13	projection		
				.XXX±.0020 / .XXX±.051	projection		
				0'±2'	projection		
				M.CORNMAN 8/10/90	INCH/MM	product family QUICKIE	code
				M.SMYK 8/10/90	5:1	size/ dwg no	sheet
				M.SMYK 8/10/90		A	2 of
				M.SMYK 8/10/90		69155	
sheet index	revision	sheet					

PRODUCT NO NOTE 6	POS	DIM A	DIM B	DIM C	STYLE
69155-X02(LF)	2X5	. 78/19. 8	. 72/18. 3	. 400/10. 16	B
-X10(LF)	2X5	. 78/19. 8	. 72/18. 3	. 400/10. 16	A
-X14(LF)	2X7	. 98/24. 9	. 92/23. 4	. 600/15. 24	C
-X16(LF)	2X8	1. 08/27. 9	1. 02/25. 9	. 700/17. 78	D
-X20(LF)	2X10	1. 28/32. 5	1. 22/31. 0	. 900/22. 86	▲
-X24(LF)	2X12	1. 48/37. 6	1. 42/36. 1	1. 100/27. 94	
-X26(LF)	2X13	1. 58/40. 1	1. 52/38. 6	1. 200/30. 48	
-X30(LF)	2X15	1. 78/45. 2	1. 72/43. 7	1. 400/35. 56	
-X34(LF)	2X17	1. 98/50. 3	1. 92/48. 8	1. 600/40. 64	
-X40(LF)	2X20	2. 28/57. 9	2. 22/56. 4	1. 900/48. 26	
-X44(LF)	2X22	2. 48/63. 0	2. 42/61. 5	2. 100/53. 34	
-X50(LF)	2X25	2. 78/70. 6	2. 72/69. 1	2. 400/60. 96	▼
69155-X60(LF)	2X30	3. 28/83. 3	3. 22/81. 8	2. 900/73. 66	D

NOTE 7

NOTE 11

A A

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCI	
ltr	ecn no	dr	date	linear	projection	title	www.fciconnect.com
M				.XX±.01/.X±.3	1	HEADER QUICKIE SLIM LINE	
				.XXX±.005/.XX±.13	2	RIGHT ANGLE 4 WALL	
				.XXX±.0020/.XXX±.051	3	QUICKIE	
				0°±2'	4	product family	code
				M.CORNMAN	5	size dwg no	69155
				M.SMYK	6	scale	3 of
				chr	7	5:1	
				appd	8		
sheet index	revision	sheet					