

### 150HV Series Heavy Duty In-line Holder for 3AB/AG



#### Product Characteristics


<b>Compatible Fuses</b>	3AB/AG Fuses
<b>Electrical</b>	Intended for use at 600 VAC/DC max rated up to 20 amperes.
<b>Molded Parts</b>	Body and knob are Black Thermoset (UL94 V-0). Both body and knob have a 0.20" diameter hole for insulated wire.
<b>Knob</b>	Bayonet-lock type metal insert.
<b>Ambient Temperature</b>	-40°C to + 85°C
<b>Contact Rivet</b>	Brass. Tin plated
<b>Assembled</b>	Supplied with 19" loop of #14 AWG red vinyl insulated wire

#### Agency Approvals

Agency	Agency File Number
	E14721

**Notes:**  
Please refer to Fuseology section for information on proper fuseholder re-rating.  
Not for use in hazardous, and/or outdoor conditions.

#### 19" Loop of 14 AWG Stranded Cu Wire



#### Ordering Information

Ordering Number	Catalog Number	Fuse Size	Packaging
01500603Z	150603	1/4" x 1 1/4"	Bulk 100 Pieces