

## Detailed Specifications

<b>Frame Width:</b>	119[mm]
<b>Frame Height:</b>	119[mm]
<b>Frame Depth:</b>	38[mm]
<b>Nominal Voltage:</b>	115[V]
<b>Frequency:</b>	60[Hz]
<b>Max. Air Flow:</b>	110[CFM]
<b>Max. Air Flow:</b>	3.1[m3 per min]
<b>Max. Static Pressure:</b>	0.37[In H2O]
<b>Max. Static Pressure:</b>	92.5[Pa]
<b>Fan Speed:</b>	3100[RPM]
<b>Noise:</b>	45[dB]
<b>Life Expectancy:</b>	25deg.C 100,000 hours[L10]
<b>Bearing Type:</b>	Ball Bearing
<b>Ingress Protection:</b>	none
<b>Starting Voltage:</b>	75[V]
<b>Input Power (+10% - 20%):</b>	14.4[V]
<b>Current:</b>	0.19[A]
<b>Mass:</b>	550[g]