

o Flat Cable Connectors SEK

o har-mik®

o D-Sub

o InduCom

Applications



Product details

09 18 506 5803

IDC female connector

Termination	Flat cable insulation displacement
Connector size	6 contacts
IDC strain relief clamp	Without strain relief
Cover	With an open end cover
Centre polarization	With central polarisation
Performance level	AU-0.76•m [30• Inch]
RoHS compliant	Yes

Available Downloads

Title	Format	
Data sheet	PDF	download
CAD data 2D	DXF	download

Further links

3D-Library



Inquiry




5

4

3



2

1



vorverrastet
pre assembled
preassemble

verrastet
fitted
assemble



1) Markierung erster Kontakt, Ader 1 des Flachkabels
1) Contact no.1, 1st wire of flat cable
1) Contact no.1, repère 1 du câble

B

C

D

A



All Dimensions in mm
Original Size DIN A 4

Techn. Character.

Nicht tolerierte Masse/ Free size tolerances

09185065803
09185066803
09185067803

0,76 μm Au
2
3

	Def.	01-FEB-00	Th
	Insp.	01-FEB-00	JMV
	Stand.		

Massstab/Scale
2:1

SEK 18 Female connector
6 poles
with central polarisation
cover without cable stop

Bestell-Nr.
Part-No.
Reference

Anforderungsstufe
performance level
Niveau de qualite

26570	01-FEB-00	JB
Mod.	Dat.	Name

HARTING EURL
F-95972 Paris



TB 0918506X803
Sub.

Blatt/ page
1/1