

ERSADUR longlife soldering tip series 832, 842 and 852



- ANALOG 60/60 A
- ANALOG 80/80 A
- DIGITAL 80 A
- DIGITAL 2000 A with POWER TOOL soldering iron
- ELS 8000/M/D

- ErsA 15+ / 25+ / 35+
- MICRO-CON 60 iA with POWER TOOL soldering iron
- MS 6000 / MS 8000/D
- MULTI-PRO
- MULTI-SPRINT

- MULTI-TC
- RDS 80
- TWIN 80 A with ERGO TOOL

<p>0832UD/UDLF</p> <p>pencil point, 0.4 mm \varnothing, extended</p>	<p>0832SD/SDLF</p> <p>pencil point, 0,8 mm \varnothing, extended</p>	<p>0832BD/BDLF</p> <p>pencil point, 1,0 mm \varnothing</p>	<p>0832YD/YDLF</p> <p>chisel-shaped, 1,6 mm</p>
<p>0832CD/CDLF</p> <p>chisel-shaped, 2,2 mm</p>	<p>0832KD/KDLF</p> <p>chisel-shaped, 2,2 mm, extended</p>	<p>0832ED/EDLF</p> <p>chisel-shaped, 3,2 mm</p>	<p>0832VD/VDLF</p> <p>chisel-shaped, 5,0 mm</p>
<p>0832FDLF</p> <p>angled face, 2,0 mm</p>	<p>0832TDLF</p> <p>angled face, 3,0 mm \varnothing</p>	<p>0832NDLF</p> <p>angled face, 4,0 mm \varnothing</p>	<p>0832PW</p> <p>PowerWell with concave portion</p>
<p>0832HD</p> <p>SolderWell with concave portion, bent</p>	<p>0832AD</p> <p>PLCC blade, 1,5 mm</p>	<p>0852OD</p> <p>PLCC blade, 2,0 mm</p>	<p>0832WD</p> <p>chisel-shaped, 2,5 mm, bent</p>
<p>0832RD</p> <p>chisel-shaped, 5,0 mm, bent</p>	<p>0832GDLF</p> <p>angled face, 14 mm, 35°</p>	<p>0832LDLF</p> <p>angled face, 17 mm, 35°</p>	<p>0832MDLF</p> <p>angled face on both sides, 8 mm</p>
<p>0842UD/UDLF</p> <p>pencil point, 0,4 mm \varnothing, extended</p>	<p>0842SD/SDLF</p> <p>pencil point, 0,8 mm \varnothing, extended</p>	<p>0842BD/BDLF</p> <p>pencil point, 1,0 mm \varnothing</p>	<p>0842YD/YDLF</p> <p>chisel-shaped, 1,6 mm</p>
<p>0842CD/CDLF</p> <p>chisel-shaped, 2,2 mm</p>	<p>0842KD/KDLF</p> <p>chisel-shaped, 2,2 mm, extended</p>	<p>0842ED/EDLF</p> <p>chisel-shaped, 3,2 mm</p>	<p>0842ID</p> <p>pencil point, 0,4 mm \varnothing, bent</p>
<p>0842JD</p> <p>chisel-shaped, 2,2 mm, bent</p>	<p>0852GD</p> <p>angled face, 8,0 mm</p>	<p>0852VD</p> <p>chisel-shaped, 5,0 mm</p>	