


| POS | DIMENSIONS(MM) |       | DIMENSIONS(MM) |       |
|-----|----------------|-------|----------------|-------|
|     | A              | B     | A              | B     |
| 2   | 2.50           | 6.50  | 10             | 22.50 |
| 3   | 5.00           | 9.00  | 11             | 25.00 |
| 4   | 7.50           | 11.50 | 12             | 27.50 |
| 5   | 10.00          | 14.00 | 13             | 30.00 |
| 6   | 12.50          | 16.50 | 14             | 32.50 |
| 7   | 15.00          | 19.00 | 15             | 35.00 |
| 8   | 17.50          | 21.50 | 16             | 37.50 |
| 9   | 20.00          | 24.00 |                |       |

- NOTE:
- ELECTRICAL CHARACTERISTICS
    - 1-1 RATING CURRENT: 3A AC/DC
    - 1-2 RATING VOLTAGE: 250V AC/DC
    - 1-3 INSULATION RESISTANCE: 1000M OHMS MIN
    - 1-4 WITHSTANDING VOLTAGE: 800V AC/1MINUTE
    - 1-5 OPERATING TEMPERATURE: -40°C~+105°C
  - MATERIAL:
    - PA66, UL 94V-0, NATURAL COLOR
  - USED WITH AFCI 10156619
  - PRODUCT SPEC: GS-12-1595
  - ORDERING CODE: 10156618-XX 0 X LF
- NUMBER OF PINS \_\_\_\_\_ PACKAGE  
02~16: 02~16PINS 0: BAG



|             |             |                      |                                       |                                       |
|-------------|-------------|----------------------|---------------------------------------|---------------------------------------|
| mat'l. code | surface     | tolerance            | projection                            | product family                        |
|             | ISO 1302    | ISO 406              | ISO 100                               | MINITEK                               |
| tr ecn no   | dr          | date                 | tolerances unless otherwise specified | title                                 |
| A           | New release | Jason Wang 2020-2-19 | .X±.3                                 | 2.5PITCH BOARD-IN, Vertical , HOUSING |
|             |             |                      | .XX±.20                               |                                       |
|             |             |                      | .XXX±.10                              |                                       |
|             |             |                      | scale 2:1                             |                                       |
| sheet       | revision    | dr                   | engr                                  | dwg no                                |
| index       | sheet       | 1                    | chr                                   | 10156618                              |
|             |             |                      | dppd                                  | sheet 1 of 1 size                     |
|             |             |                      |                                       | A3                                    |
|             |             |                      |                                       | Product Customer Drawing              |