


ORDERING INFORMATION



TECHNICAL SPECIFICATION

INSULATOR MATERIAL : SELF EXTINGUISHING THERMOPLASTIC (UL94 VO)
 CONTACT MATERIAL : COPPER ALLOY
 MAXIMUM VOLTAGE : 500 V rms.
 NOMINAL CURRENT : 3A AT 20°C
 INSULATION RESISTANCE : > 1000 MΩ
 CLIMATIC CATAGORY : -55°C TO +125°C / 21 DAYS EXPOSURE TO- INDUSTRIAL ENVIRONMENT HUMIDITY TEST AS HE-14.
 CONTACT RESISTANCE : < 20mΩ

NOTES :
 1. THE PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-47-004

mat'l. code				surface		tolerance		projection		product family			
REF TECH SPEC				ISO 1302		ISO 406 ISO 1101		MM		8614			
ltr	ecn no	dr	date	tolerances unless otherwise specified						title			
C	I06-0124	MKV	2002-07-12	angles	linear	.0±0.1				FEMALE SHORTING PLUG (CLOSED)			
D	I06-0126	MKV	2003-06-07										
E	I06-0127	MKV	2004-09-29	0°±1°				scale -					
F	I06-0116	AB	2006-07-20	dr	MINI K VANDANATH	1998-12-06				dwg no		sheet 1 of 1	size
G	ELX-I-19435	GMA	2014-11-15	enr	JAI.K.A	1998-12-06				C-8614-0085		A3	
H	ELX-I-24519	GMA	2016-07-15	chr	GREGAR.M	2016-07-15				type		Product Customer	Drawing
				appd	BIJU K P	2016-07-15							
sheet index	revision sheet	C	D	E	F	G	H						
		1	1	1	1	1	1						