

# Alubos

## Enclosure profiles, closed



ABP 800-0200

Order no.: 84080200

\* = Available on request.

### Characteristics

Colour of enclosure group

Black, similar to RAL 9005

Protection class

IP 65

Enclosure Material

Extruded profiles: Al Mg Si 0.5 powder-coated; diecast lid: GB Al Si 12, powder-coated; seal: TPE; for details see Technical Information

### Scope of delivery

Enclosure profile

### Note


C = profile length, special lengths on request.

### Dimensions

Dimensions

82 x 32 x 200 mm

Product drawing



### Important!

To compensate for pressure when temperatures change and cause moisture in the enclosure, we recommend that you use a pressure compensation element.

» Additional information

## Technical documentation / Downloads

---

### Technical drawings

3D product data in STEP format: Registration necessary  
Product drawing in PDF format: 84080200 ABP-800-0200.pdf (105.8 KB)  
Product drawing in DXF format: 84080200 ABP-800-0200.dxf (1.1 MB)  
Drawing for mechanical processing: 84080200 ABP-800-0200-G.dxf (259.9 KB)

Milling contours are shown here as a DXF file. (Sub D, USB, HDMI, cable glands, ...)

### Product information

Alubos GB.pdf (2.7 MB)

## Matching accessories

---



End cover

84081000 ABD 800

For AB 800



Mounting lid with removable aluminium cap

84082000 ABM 800 AL

For AB 800



Mounting lid with hinged aluminium flap

84084000 ABM 800 SAL

For AB 800



Mounting lid with removable aluminium cap and compartment for 9V block battery

84082100 ABM 800 AL BE

For AB 800



Mounting lid with hinged aluminium flap and compartment for 9V block battery

84084100 ABM 800 SAL-BE

For AB 800



Mounting lid with infrared-permissive plastic cap

84083000 ABM 800 IR

For AB 800



Mounting lid with infrared-permissive plastic cap and compartment for 9V block battery

84083100\* ABM 800 IR BE For AB 800



EMC seals

84200815 DI 800-EMV For AB 800



Seals, ultramarine

84200814 DI 800-5002 For AB 800



Seals, fire red

84200811 DI 800-3000 For AB 800



Seals, rape yellow

84200812 DI 800-1021 For AB 800



Seals, patina green

84200813 DI 800-6000 For AB 800



Seals UL 94 V0

84200819\* DI 800-V0 For AB 800



Wall brackets, sheet steel

84005000 AB-WL For AB 600/800/1000/1300



Wall brackets, adjustable, sheet steel

84085000 AB-800 WLV For AB 800/820



### Mounting clamps

84006300 AB-MKL  
84006400 AB 800 MKL

For AB 600/800/1000  
For AB 800



### Rubber feet

84006700 AB - GF

Polyurethane, 65-75 Shore

Black