


Coding style table	
	Style A: For connectors 6 poles
	Style B: For connectors 10 and 14 poles
	Style C: For connectors from 16 to 64 poles

-Technical information available on a separate document ref: DS 09191130202
-Full range of P/N's and dimensions shown on page 2/2



	All rights reserved Department EC PD - FR	Created by DOUGE	Inspected by BAGDIKIAN	Standardisation HOFFMANN	Date 2014-05-16	State Final Release	Ref. Sub.
	HARTING Electronics GmbH D-32339 Espelkamp	Title SEK 19 male straight low profile		Doc-Key / ECM-Nr. 100565939/UGD/001/A 50000068837		Rev. A	Page 1/2
All Dimensions in mm Original Size DIN A3		Scale 2:1	Free size tol.				
		Type TB	Number 09195XXX324				


A

B

C

D

Nb of Contacts	Performance Level			Insulator Color	Accessory	Dimensions (mm)				
	PL3	PL2	S4			A Max	B	E		
06	0919 506 7324	0919 506 6324	0919 506 5324	Beige	-	15,4	12,78	2,54 x 2 = 5,08		
10	0919 510 7324	0919 510 6324	0919 510 5324			20,5	17,86	2,54 x 4 = 10,16		
14	0919 514 7324	0919 514 6324	0919 514 5324			25,6	22,94	2,54 x 6 = 15,24		
16	0919 516 7324	0919 516 6324	0919 516 5324			28,1	25,48	2,54 x 7 = 17,78		
20	0919 520 7324	0919 520 6324	0919 520 5324			33,2	30,56	2,54 x 9 = 22,86		
26	0919 526 7324	0919 526 6324	0919 526 5324			40,8	38,18	2,54 x 12 = 30,48		
30	0919 530 7324	0919 530 6324	0919 530 5324			45,9	43,26	2,54 x 14 = 35,56		
34	0919 534 7324	0919 534 6324	0919 534 5324			51,0	48,34	2,54 x 16 = 40,64		
40	0919 540 7324	0919 540 6324	0919 540 5324			58,6	55,96	2,54 x 19 = 48,26		
50	0919 550 7324	0919 550 6324	0919 550 5324			71,5	68,66	2,54 x 24 = 60,96		
60	0919 560 7324	0919 560 6324	0919 560 5324			84,2	81,36	2,54 x 29 = 73,66		
64	0919 564 7324	0919 564 6324	0919 564 5324			89,3	86,44	2,54 x 31 = 78,74		
06	0919 506 7324 001	0919 506 6324 001	0919 506 5324 001			Black	-	15,4	12,78	2,54 x 2 = 5,08
10	0919 510 7324 001	0919 510 6324 001	0919 510 5324 001					20,5	17,86	2,54 x 4 = 10,16
14	0919 514 7324 001	0919 514 6324 001	0919 514 5324 001	25,6	22,94			2,54 x 6 = 15,24		
16	0919 516 7324 001	0919 516 6324 001	0919 516 5324 001	28,1	25,48			2,54 x 7 = 17,78		
20	0919 520 7324 001	0919 520 6324 001	0919 520 5324 001	33,2	30,56			2,54 x 9 = 22,86		
26	0919 526 7324 001	0919 526 6324 001	0919 526 5324 001	40,8	38,18			2,54 x 12 = 30,48		
30	0919 530 7324 001	0919 530 6324 001	0919 530 5324 001	45,9	43,26			2,54 x 14 = 35,56		
34	0919 534 7324 001	0919 534 6324 001	0919 534 5324 001	51,0	48,34			2,54 x 16 = 40,64		
40	0919 540 7324 001	0919 540 6324 001	0919 540 5324 001	58,6	55,96			2,54 x 19 = 48,26		
50	0919 550 7324 001	0919 550 6324 001	0919 550 5324 001	71,5	68,66			2,54 x 24 = 60,96		
60	0919 560 7324 001	0919 560 6324 001	0919 560 5324 001	84,2	81,36			2,54 x 29 = 73,66		
64	0919 564 7324 001	0919 564 6324 001	0919 564 5324 001	89,3	86,44			2,54 x 31 = 78,74		
06	0919 506 7324 740	0919 506 6324 740	0919 506 5324 740	Beige	Vacuum Cover			15,4	12,78	2,54 x 2 = 5,08
10	0919 510 7324 740	0919 510 6324 740	0919 510 5324 740					20,5	17,86	2,54 x 4 = 10,16
14	0919 514 7324 740	0919 514 6324 740	0919 514 5324 740			25,6	22,94	2,54 x 6 = 15,24		
16	0919 516 7324 740	0919 516 6324 740	0919 516 5324 740			28,1	25,48	2,54 x 7 = 17,78		
20	0919 520 7324 740	0919 520 6324 740	0919 520 5324 740			33,2	30,56	2,54 x 9 = 22,86		
26	0919 526 7324 740	0919 526 6324 740	0919 526 5324 740			40,8	38,18	2,54 x 12 = 30,48		
30	0919 530 7324 740	0919 530 6324 740	0919 530 5324 740			45,9	43,26	2,54 x 14 = 35,56		
34	0919 534 7324 740	0919 534 6324 740	0919 534 5324 740			51,0	48,34	2,54 x 16 = 40,64		
40	0919 540 7324 740	0919 540 6324 740	0919 540 5324 740			58,6	55,96	2,54 x 19 = 48,26		
50	0919 550 7324 740	0919 550 6324 740	0919 550 5324 740			71,5	68,66	2,54 x 24 = 60,96		
60	0919 560 7324 740	0919 560 6324 740	0919 560 5324 740			84,2	81,36	2,54 x 29 = 73,66		
64	0919 564 7324 740	0919 564 6324 740	0919 564 5324 740			89,3	86,44	2,54 x 31 = 78,74		
06	0919 506 7324 741	0919 506 6324 741	0919 506 5324 741			Black	Vacuum Cover	15,4	12,78	2,54 x 2 = 5,08
10	0919 510 7324 741	0919 510 6324 741	0919 510 5324 741					20,5	17,86	2,54 x 4 = 10,16
14	0919 514 7324 741	0919 514 6324 741	0919 514 5324 741	25,6	22,94			2,54 x 6 = 15,24		
16	0919 516 7324 741	0919 516 6324 741	0919 516 5324 741	28,1	25,48			2,54 x 7 = 17,78		
20	0919 520 7324 741	0919 520 6324 741	0919 520 5324 741	33,2	30,56			2,54 x 9 = 22,86		
26	0919 526 7324 741	0919 526 6324 741	0919 526 5324 741	40,8	38,18			2,54 x 12 = 30,48		
30	0919 530 7324 741	0919 530 6324 741	0919 530 5324 741	45,9	43,26			2,54 x 14 = 35,56		
34	0919 534 7324 741	0919 534 6324 741	0919 534 5324 741	51,0	48,34			2,54 x 16 = 40,64		
40	0919 540 7324 741	0919 540 6324 741	0919 540 5324 741	58,6	55,96			2,54 x 19 = 48,26		
50	0919 550 7324 741	0919 550 6324 741	0919 550 5324 741	71,5	68,66			2,54 x 24 = 60,96		
60	0919 560 7324 741	0919 560 6324 741	0919 560 5324 741	84,2	81,36			2,54 x 29 = 73,66		
64	0919 564 7324 741	0919 564 6324 741	0919 564 5324 741	89,3	86,44			2,54 x 31 = 78,74		

	All Dimensions in mm Original Size DIN A4		Scale 1:1	Free size tol.		Ref.	
	All rights reserved		Created by DOUGE	Inspected by BAGDIKIAN	Standardisation HOFFMANN	Date 2014-05-16	State Final Release
Department EC PD - FR		Title SEK 19 male straight low profile				Doc-Key / ECM-Nr. 100565939/UGD/001/A 500000068837	
HARTING Electronics GmbH D-32339 Espelkamp		Type TB	Number 09195XXX324			Rev. A	Page 2/2