

Rittal – The System.

Faster – better – everywhere.

FlatBox – DK 7507.000

Date : Apr 27, 2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



FlatBox – DK 7507.000

created: 27.04.2021 build on www.rittal.com/uk-en



Product description

Design:	with 482.6 mm (19") mounting angles
Description:	For flexible use as a wall-mounted or floor-standing enclosure.
Benefits:	Tool-free quick assembly System assembly on the open 482.6 mm (19") frame
Material:	Sheet steel Viewing window: Single-pane safety glass, 3 mm
Surface finish:	Powder-coated
Colour:	RAL 7035
Supply includes:	Flat-packed enclosure 1 wall section 2 basic supports 2 roof/base plates, with cut-outs for cable entry via brush strips 2 side panels, lockable 1 glazed door, lockable, security lock 3524 E, door hinge point selectable Connection components for tool-free, fast assembly Earthing kit for system-compatible earthing of all enclosure parts 482.6 mm (19") mounting angles
Note:	Max. installation depth: Depth - 58 mm to rear panel Max. distance between two 482.6 mm (19") levels: Depth - 104 mm
Basic material:	Sheet steel

Product description

Dimensions:	Width: 600 mm Height: 358 mm Depth: 400 mm
Installation height for components:	6 U
Load capacity:	max. 300 N
Packs of:	1 pc(s).
Weight/pack:	17.84 kg
EAN:	4028177551398
Customs tariff number:	94032080
ETIM 7.0:	EC002500
ETIM 6.0:	EC002500
eCl@ss 8.0/8.1:	27180208
eCl@ss 6.0/6.1:	27180208
Product description:	DK FlatBox, WHD: 600x358x400 mm, 6 U, with 482.6 mm (19") mounting angles
Approvals	
Certificates:	NA