

Number of contacts

**9-37**



Insulation displacement termination

Identification	No. of contacts	Part No.	
<b>Performance levels</b> Explanations see page 05.04 Other performance levels on request		Performance level <b>3</b>	
		Performance level <b>2</b>	
<b>Male connector<sup>2)</sup></b> pitch 1.27 mm metal shell with dimples	9 15 25 37	09 66 128 770 . 09 66 228 770 . 09 66 328 770 . 09 66 428 770 .	09 66 128 670 . 09 66 228 670 . 09 66 328 670 . 09 66 428 670 .
<b>Female connector<sup>2)</sup></b> pitch 1.27 mm metal shell	9 15 25 37	09 66 118 750 . 09 66 218 750 . 09 66 318 750 . 09 66 418 750 .	09 66 118 650 . 09 66 218 650 . 09 66 318 650 . 09 66 418 650 .
Please insert digit for flange thread			
ø 3.1 mm hole ▶ 0 M3 ▶ 1 <sup>1)</sup> 4-40 UNC ▶ 2			
<b>Strain relief clamp</b> plastic for male and female connector	9 15 25 37	09 66 108 001 09 66 208 001 09 66 308 001 09 66 408 001	09 66 108 001 09 66 208 001 09 66 308 001 09 66 408 001

<sup>1)</sup> Not normally kept in stock  
<sup>2)</sup> Not released for halogen free flat cables