

Alnico Rectangular Bar Magnet datasheet

- Alnico 5 magnet material
- Magnetically stable at high temperatures
- Max. operating temperature 220°C
- Mild steel pot, aluminium spacer.
- Zinc plated body
- Diameter ground to H6 tolerance
- Custom designs available
- Sold in pairs. North pole is indicated by a notch/dimple



Product Information

Product No.	Material	Length*	Width	Height	Weight / pair	Gauss
E844	Alnico 5	20	10 <i>mm</i>	5	0.030 <i>kg</i>	1100
E845	"	40	12.5	5	0.040	1100
E846	"	60	15	5	0.130	1100

*magnetic axis