

quick connector CK-3/8-PK-9-KU

Part number: 6468

FESTO

Male thread with sealing rim, polymer design.



Data sheet

Feature	Value
Nominal size	8 mm
Type of seal on screw-in stud	Sealing edge
Assembly position	Any
Operating pressure complete temperature range	0 ... 10 bar
Maritime classification	see certificate
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-] Water as per manufacturer's declaration at www.festo.com
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Ambient temperature	-10 ... 60 °C
Pneumatic connection, port 1	Male thread G3/8
Pneumatic connection, port 2	For tubing internal diameter 9 mm
Materials note	Conforms to RoHS
Material housing	POM