



product details

QTP-M 2X26-32/220-240 S UNV1

Product description: QTP-M 2X26-32/220-240 S UNV1 ¹⁾
 Product code: 4008321329158
 Quantity: Unpacked (UNV) contains 1 Piece (PCE)

You can find this product in the eCatalog:

http://catalog.myosram.com?~language=EN&~country=COM&it_p=4008321329158

| Capabilities | |
|--|---|
| Suitable for fixtures with prot. class | Class I Class II |
| Dimmable | No |
| Country specific categorizations | |
| SEG number | 7980317 |
| Certificates & standards | |
| Approval marks - approval | E1 approval VDE VDE-EMC |
| EEL - Energy Label | A2 |
| Standards | acc. to EN 61347-2-3 acc. to EN 60929 acc. to EN 55015:2006 + A1:2007 acc. to EN 61000-3-2 acc. to EN 61547 |
| Type of protection | IP20 |
| Additional product data | |
| Design / version | ECG multiwatt |
| New article | NEW |
| Logistical data | |
| Relative humidity | 5...85 % ²⁾ |
| Temperature range at storage | -40...85 °C |
| Electrical data | |
| Nominal wattage + Power loss | 0 |
| Maximum mains current | 0.30 A |
| Nominal voltage | 220-240 V |
| Mains frequency | 50...60 Hz |
| DC voltage | 176...276 V |
| Operating frequency | 45 kHz ³⁾ |
| Dielectric strength | 300 V 320 V 350 V ⁴⁾ |
| Max. no. of ECGs on circuit breaker 10 A | 17 |
| Max. no. of ECGs on circuit breaker 16 A | 28 |
| TH full width at half maximum | 250 µs |
| Dimensions & weight | |
| Length | 123.00 mm |
| Width | 79.00 mm |
| Height | 33.00 mm |
| Mounting hole spacing, length | 129.5 mm |
| Mounting hole spacing, width | 67 mm |
| Product weight | 180 g |
| Light technical data | |
| Rated starting time | preheat start within 1.0 s |





| Temperatures | |
|---|--------------|
| Ambient temperature range | -20...+50 °C |
| Operating temperature | 70 °C |
| Max. housing temperature in case of fault | 110 °C |

| Packaging units | | | | |
|-----------------|---------------------------------------|-------------------------------------|-----------------------|------------------|
| Product code | Packaging type and content | Dimensions in h x w x l | Gross weight | Volume |
| 4008321329158 | Unpacked contains 1 Piece | 80,000 mm x 33,000 mm x 123,000 mm | 180,000 g (0,000 g) | 0,327 Cubic dec. |
| 4008321329165 | Shipping carton box contains 20 Piece | 257,000 mm x 88,000 mm x 428,000 mm | 3 860,000 g (0,000 g) | 8,580 Cubic dec. |

- 1) Optional cable clamp, see chapter ECG mountings - cable clamp
- 2) Maximum 56 days/year at 85 %
- 3) Approximately
- 4) Permanent | 48 h | 2 h



Lamp wiring:



- 3) Max. permitted cable length in between ECG and lamp: 2.0 m (PIN 21; 22); 1.0 m (PIN 23; 24)
4) Max. permitted cable length in between ECG and lamp: 2.0 m (PIN 21; 22); 1.0 m (PIN 25; 26)