


Metal-Fitting S




Material	Nickel plated brass
Protection Category	IP 54
Operating Temperature	-20 °C – +80 °C (-4 °F – +176 °F)

RoHS

- // Swivel conduit fitting
- // Locknut optional



AG	d mm	GL mm	H mm	 mm	fits to Metal- Conduit DN	Number
M 12	6	8	27	15	7	1.571.1260.50
M 16	7	8	27	20	9	1.571.1660.51
M 16	9	10	29	20	11	1.571.1660.50
M 20	12	10	29	22	14	1.571.2060.51
M 20	14	10	29	22	16	1.571.2060.50
M 25	18	10	31	28	21	1.571.2560.50
M 32	23	12	35	35	26	1.571.3260.50
M 40	33,5	14	41	45	37	1.571.4060.50
M 50	37	14	41	55	40	1.571.5060.50
M 63	46	14	41	65	51	1.571.6360.50
PG 7	6	8	27	15	7	1.571.0760.14
PG 9	7	8	27	17	9	1.571.0960.14
PG 11	9	10	29	20	11	1.571.1160.14
PG 13,5	12	10	29	22	14	1.571.1360.14
PG 16	14	10	29	24	16	1.571.1660.14
PG 21	18	10	31	30	21	1.571.2160.14
PG 29	23	12	35	40	26	1.571.2960.14
PG 36	33,5	14	41	50	37	1.571.3660.14
PG 42	37	14	41	60	40	1.571.4260.14
PG 48	46	14	41	65	51	1.571.4860.14
NPT 1/4"	6	10	29	15	7	1.571.1460.70
NPT 3/8"	7	11,5	30,5	20	9	1.571.3860.71
NPT 3/8"	9	11,5	30,5	20	11	1.571.3860.70
NPT 1/2"	12	13	32	22	14	1.571.1260.71
NPT 1/2"	14	13	32	22	16	1.571.1260.70
NPT 3/4"	18	15	36	28	21	1.571.3460.70
NPT 1"	23	15	39	35	26	1.571.1060.70
NPT 1 1/4"	33,5	16	43	45	37	1.571.5460.70
NPT 1 1/2"	37	18	45	55	40	1.571.6460.70
NPT 2"	46	20	47	65	51	1.571.2060.70