



3889 - COMPACT MALE STUD ELBOW BSP TAPER THREAD



maximum working pressure	20 bar 2 MPa 290 psi
working temperature	-25 to 150 °C -13 to 302 °F 248 to 423 °K
vacuum capability	755 mm Hg
body	STAINLESS STEEL 316L
sub-base	STAINLESS STEEL 316L
'O'-rings	FKM
collar	STAINLESS STEEL 316L
sealing washer	STAINLESS STEEL 316L

Part Nb	ØD (MM)	C	F (mm)	ØG (mm)	H (mm)	L (mm)	(kg)
	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>
3889 04 10	4	R1/8	13	10	18	17	.019
3889 04 13	4	R1/4	17	10	19.5	16.5	.018
3889 06 10	6	R1/8	13	12	21.5	20.5	.025
3889 06 13	6	R1/4	14	12	21.5	20.5	.032
3889 08 10	8	R1/8	14	15	24	22	.036
3889 08 13	8	R1/4	14	15	24	22	.036
3889 10 13	10	R1/4	17	17.5	28.5	27.5	.058
3889 10 17	10	R3/8	19	17.5	28.5	27.5	.068
3889 12 13	12	R1/4	22	20	33.5	30	.088
3889 12 17	12	R3/8	22	20	33.5	30	.09
3889 12 21	12	R1/2	22	20	33.5	33	.097