



## A088



### HSS Stub Drill Set with A022 Drills, TiN-Tip Coated

A set containing 24 different diameters of the A022 stub drill in a sturdy case, for a wide range of hole sizes covered with a single purchase. The drills are suitable for use both in machines and hand-held drilling in many applications. TiN-Tip coating improves performance and extends tool life.

HSS	DIN ANSI	2.5×D
135°	TiN-Tip	
20-35°	R	DC h8

A=Styles in Set, B=No. in Set, C=Diameters in Set.

Product	Nr.	A	B	C
A0882005	2005	A022	24	1.0 mm - 10.5 mm x 0.5 mm + 3.3 mm, 4.2 mm, 6.8 mm, 10.2 mm

## A095



### HSS Jobber Drill Set with A002 Drills, TiN-Tip Coated

Different sets in metric or fractional sizes of our A002 drills in a useful plastic storage case. The set keeps all drills together, with sizes clearly displayed for easy selection. The drills are suitable for use in both machines and hand-held applications. TiN-Tip coating improves performance and extends tool life.

HSS	DIN 338	4×D
118°	TiN-Tip	
20-35°	R	DC h8

1.0mm =< DC >= 2.9mm 118° 4 Facet Point. A=Styles in Set, B=No. in Set, C=Diameters in Set.

Product	Nr.	A	B	C
A09518	18	A002	29	1/16 inch - 1/2 inch x 1/64 inch
A09520	20	A002	15	1/16 inch - 1/2 inch x 1/32 inch
A095200	200	A002	24	1.0 mm - 10.5 mm x 0.5 mm + 3.3 mm, 4.2 mm, 6.8 mm, 10.2 mm
A095201	201	A002	19	1.0 mm - 10.0 mm x 0.5 mm
A095202	202	A002	51	1.0 mm - 6.0 mm x 0.1 mm
A095203	203	A002	41	6.0 mm - 10.0 mm x 0.1 mm
A095204	204	A002	25	1.0 mm - 13.0 mm x 0.5 mm
A095206	206	A002	29	1.0 mm - 13.0 mm x 0.5 mm + 3.3 mm, 4.2 mm, 6.8 mm, 10.2 mm
A095209	209	A002	91	1.0 mm - 10.0 mm x 0.1 mm