






# GST 18i 3 pole 250 V, 16 A

				Extender lead		Starter lead		Connection lead	
<b>Cable: H05VV-F3G1.5/2.5</b>  <b>Insulation: with halogen (PVC)</b>				<b>3 x 1.5 mm<sup>2</sup></b>  <b>female – male</b>		<b>3 x 1.5 mm<sup>2</sup></b>  <b>female – free end</b> with ultrasonically welded conductor ends <sup>1)</sup>		<b>3 x 1.5 mm<sup>2</sup></b>  <b>male – free end</b> with ultrasonically welded conductor ends <sup>1)</sup>	
<b>Cable assemblies</b>				Standard PVC cable Type H05VV-F3G1.5 Colour black					
									
Application	Coding	Colour	Length <sup>2)</sup>	Part No.	Box Qty	Part No.	Box Qty	Part No.	Box Qty
Mains with earth	Code 1 Female  Male 	black	1.0 m	92.232.1000.1	75	92.232.1003.1	75	92.232.1004.1	75
			2.0 m	92.232.2000.1	40	92.232.2003.1	50	92.232.2004.1	50
			3.0 m	92.232.3000.1	25	92.232.3003.1	25	92.232.3004.1	25
			4.0 m	92.232.4000.1	25	92.232.4003.1	25	92.232.4004.1	25
			5.0 m	92.232.5000.1	20	92.232.5003.1	20	92.232.5004.1	20
			6.0 m	92.232.6000.1	10	92.232.6003.1	10	92.232.6004.1	10
			7.0 m	92.232.7000.1	10	92.232.7003.1	10	92.232.7004.1	10
			8.0 m	92.232.8000.1	10	92.232.8003.1	10	92.232.8004.1	10
	Code 2	grey	1.0 m	92.232.1000.2	75	92.232.1003.2	75	92.232.1004.2	75
			2.0 m	92.232.2000.2	40	92.232.2003.2	50	92.232.2004.2	50
			3.0 m	92.232.3000.2	25	92.232.3003.2	25	92.232.3004.2	25
			4.0 m	92.232.4000.2	25	92.232.4003.2	25	92.232.4004.2	25
			5.0 m	92.232.5000.2	20	92.232.5003.2	20	92.232.5004.2	20
			6.0 m	92.232.6000.2	10	92.232.6003.2	10	92.232.6004.2	10
			7.0 m	92.232.7000.2	10	92.232.7003.2	10	92.232.7004.2	10
			8.0 m	92.232.8000.2	10	92.232.8003.2	10	92.232.8004.2	10
	Code 3	light red	1.0 m	92.232.1000.3	75	92.232.1003.3	75	92.232.1004.3	75
			2.0 m	92.232.2000.3	40	92.232.2003.3	50	92.232.2004.3	50
			3.0 m	92.232.3000.3	25	92.232.3003.3	25	92.232.3004.3	25
			4.0 m	92.232.4000.3	25	92.232.4003.3	25	92.232.4004.3	25
			5.0 m	92.232.5000.3	20	92.232.5003.3	20	92.232.5004.3	20
			6.0 m	92.232.6000.3	10	92.232.6003.3	10	92.232.6004.3	10
			7.0 m	92.232.7000.3	10	92.232.7003.3	10	92.232.7004.3	10
			8.0 m	92.232.8000.3	10	92.232.8003.3	10	92.232.8004.3	10
	cable: black	1.0 m	92.232.1000.5	75	92.232.1003.5	75	92.232.1004.5	75	
		2.0 m	92.232.2000.5	40	92.232.2003.5	50	92.232.2004.5	50	
		3.0 m	92.232.3000.5	25	92.232.3003.5	25	92.232.3004.5	25	
		4.0 m	92.232.4000.5	25	92.232.4003.5	25	92.232.4004.5	25	
		5.0 m	92.232.5000.5	20	92.232.5003.5	20	92.232.5004.5	20	
		6.0 m	92.232.6000.5	10	92.232.6003.5	10	92.232.6004.5	10	
		7.0 m	92.232.7000.5	10	92.232.7003.5	10	92.232.7004.5	10	
		8.0 m	92.232.8000.5	10	92.232.8003.5	10	92.232.8004.5	10	