


LTE Flat Rotation Antenna Specification



Main Technical Specifications

Frequency	700-2700Mhz
Frequency range	791-960/1710-2170/2570-2620Mhz
Gain	5dBi
VSWR	≤2.0:1
Input Impedance	50ohm
Radiation	OMNI
Polarization Type	Vertical
Max Input power	50w
Antenna Length	196mm
Connector Type	SMA /ME etc.
Antenna Color	Black
Storage Temperature	-30°C to +75°C

Characteristic curve



Size drawing

