

Product data sheet

Specifications



Metal industrial cut-out box - low plain cover - H85xW85xD49 - IP55 - grey

NSYDB88M

Main

Range of product	Spacial SDB
Device application	Multi-purpose
Product or component type	Junction box
Enclosure type	Empty enclosure
Type of front cover	Low plain cover
Colour	Light grey (RAL 7035)

Complementary

Enclosure nominal height	85 mm
Enclosure nominal width	85 mm
Enclosure nominal depth	49 mm
Enclosure mounting	Wall mounted
Device composition	1 body 1 cover 1 cover screw
Cable entry number	1 diameter: 20.5 mm (M20) 1 diameter: 25.5 mm (M25)
Cover fixing	Screw
Material	Steel
Surface finish	Epoxy-polyester powder
Net weight	0.191 kg

Environment

Standards	IEC 62208
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 62262

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	191 g

Package 1 Height	5.5 cm
Package 1 width	9 cm
Package 1 Length	9 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)