

GRM31BR73A472KW01#

“#” indicates a package specification code.



< List of part numbers with package codes >

GRM31BR73A472KW01L GRM31BR73A472KW01K

Appearance & Shape



References

Packaging	Specifications	Minimum Order Quantity
L	180Embossed Tape	3000
K	330Embossed Tape	10000

Mass (typ.)	
1 piece	40mg
φ180mm Reel	170g

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

GRM31BR73A472KW01#

“#” indicates a package specification code.

Specifications

Length	3.2±0.2mm
Width	1.6±0.2mm
Thickness	1.25+0/-0.3mm
Capacitance	4700pF ±10%
Distance between external terminals g	1.2mm min.
External terminal size e	0.3mm min.
Operating Temperature Range	-55°C to 125°C
Rated Voltage	1000Vdc
Size code in inch(mm)	1206 (3216M)
Capacitance change rate	±15.0%
Temperature characteristics (complied standard)	X7R(EIA)
Temperature range of temperature characteristics	-55°C to 125°C

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.


Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

GRM31BR73A472KW01#


“#” indicates a package specification code.

Characteristic Data


The charts below may show another part number which shares its characteristics.




■ GRM31BR73A472KW01 |Z| DCOV, 25degC



■ GRM31BR73A472KW01 R DCOV, 25degC



■ GRM31BR73A472KW01 C-DC bias capchange, 25.0degC, AC1V



■ GRM31BR73A472KW01 C-AC Voltage capchange, DCOV, 25.0d

Attention



1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

GRM31BR73A472KW01#

“#” indicates a package specification code.



Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
 - 2.This datasheet has only typical specifications because there is no space for detailed specifications.
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.