



# IDM160-411S USB Kit

IDM

MOBILE HANDHELD SCANNERS

**SICK**  
Sensor Intelligence.



### Ordering information

Type	Part no.
IDM160-411S USB Kit	6080733

**Included in delivery:** IDM160-411S (1), Connection cable (1)

Should you require further technical data, this can be found with the single scanner and the other parts of the kit.

Other models and accessories → [www.sick.com/IDM](http://www.sick.com/IDM)



### Detailed technical data

#### Features

<b>Version</b>	Standard Range
<b>Application</b>	Industrial application
<b>Scanner design</b>	Cable connection variant
<b>Light source</b>	LED, Visible, Red, 630 nm
<b>Reading distance</b>	20 mm ... 850 mm <sup>1)</sup>
<b>Scanning frequency</b>	≤ 500 Hz
<b>Code resolution</b>	≥ 0.076 mm

<sup>1)</sup> For details see reading field diagram.

#### Mechanics/electronics

<b>Supply voltage</b>	5 V DC, ± 10 %
<b>Current consumption</b>	Operation (vibration activated): 230 mA Operation (vibration deactivated): 180 mA Standby: 80 mA
<b>Housing color</b>	Blue, gray
<b>Enclosure rating</b>	IP65
<b>Weight</b>	208 g, without cable
<b>Dimensions (L x W x H)</b>	104 mm x 76.3 mm x 176 mm

#### Performance

<b>Readable code structures</b>	1D codes, Stacked
<b>Bar code types</b>	Code 39, Code 39 Full ASCII, Code 32, Code 128, GS1-128, Codabar, Code 11, Code 93, GS1 DataBar, Standard and Industrial 2 of 5, Interleaved & Matrix 2 of 5, IATA, UPC / EAN / JAN, UPC / EAN / JAN (with addition), Telepen, MSI/Plessey, UK/Plessey, Australian Post, China Post, German Post, US Planet, US Postnet, British Post, Intelligent Mail, Japan Post, Korea Post, Dutch KIX Post, Posi LAPA 4 State Code
<b>Stacked code types</b>	PDF417, MicroPDF417, Composite Code

#### Interfaces

<b>USB</b>	✓
------------	---

	Function	Keyboard wedge, COM-Port emulation
<b>Optical indicators</b>		2 LEDs (operational status, good read)
<b>Acoustic indicators</b>		Beeper, can be switched off
<b>Vibration</b>		Yes
<b>Configuration software</b>		IDM Setup Tool

#### Ambient data

<b>Shock resistance</b>	50 drops from 2 m height on concrete
<b>Ambient operating temperature</b>	-10 °C ... +50 °C
<b>Storage temperature</b>	-40 °C ... +70 °C
<b>Permissible relative humidity</b>	± 95 %, Non-condensing
<b>Ambient light immunity</b>	100,000 lx

#### General notes

<b>Note</b>	Not free of paint wetting impairment substances.
-------------	--


#### Classifications

<b>eCl@ss 5.0</b>	27280101
<b>eCl@ss 5.1.4</b>	27280101
<b>eCl@ss 6.0</b>	27280101
<b>eCl@ss 6.2</b>	27280101
<b>eCl@ss 7.0</b>	27280101
<b>eCl@ss 8.0</b>	27280101
<b>eCl@ss 8.1</b>	27280101
<b>eCl@ss 9.0</b>	27280101
<b>eCl@ss 10.0</b>	27280101
<b>eCl@ss 11.0</b>	27280101
<b>eCl@ss 12.0</b>	27280101
<b>ETIM 5.0</b>	EC002550
<b>ETIM 6.0</b>	EC002550
<b>ETIM 7.0</b>	EC002550
<b>ETIM 8.0</b>	EC002550
<b>UNSPSC 16.0901</b>	43211701

### Connection diagram


PROFINET IO/RT

#### PROFINET IO/RT




PROFIBUS DP

PROFIBUS DP




Ethernet TCP/IP

### Ethernet TCP/IP



EtherCAT®

EtherCAT®




DeviceNet™

## DeviceNet™



AUX looping


## Looping-in via AUX






## Selection Guide

### IDMx4x




#### Accessories




# IDM160-411S USB Kit | IDM

## MOBILE HANDHELD SCANNERS

### IDMx6x




### Accessories





## Recommended accessories

Other models and accessories → [www.sick.com/IDM](http://www.sick.com/IDM)

	Brief description	Type	Part no.
<b>Other mounting accessories</b>			
	Tripod mount	Stand mount	6045193
	Desk holder	Table mount	6045192

### Recommended services

Additional services → [www.sick.com/IDM](http://www.sick.com/IDM)

	Type	Part no.
Extended warranty		
<ul style="list-style-type: none"><li>• <b>Product area:</b> Identification solutions, machine vision, Distance sensors, Detection and ranging solutions</li><li>• <b>Range of services:</b> The services correspond to the scope of the statutory manufacturer warranty (SICK general terms of delivery).</li><li>• <b>Duration:</b> Five-year warranty from delivery date.</li></ul>	Extended warranty for a total of five years from delivery date	1680671

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)