



6911 - MALE STUD FITTING STAINLESS STEEL 316L EPDM SEAL



maximum working pressure	16 bar 2 MPa 232 psi
working temperature	-10 to 130 °C 14 to 266 °F 263 to 403 °K
vacuum capability	755 mm Hg
body	STAINLESS STEEL 316L
'O'-rings	EPDM
gripping ring	STAINLESS STEEL

Part Nb	ØD (MM)	C	E (mm)	F (mm)	(mm)	H (mm)	(kg)
	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾
6911 04 10	4	G1/8	4.5	13	3	11.5	.007
6911 04 13	4	G1/4	5.5	16	3	10.5	.011
6911 04 19	4	M5x0,8	3	10	2.5	14	.006
6911 06 10	6	G1/8	4.5	13	4	13	.007
6911 06 13	6	G1/4	5.5	16	4	12.5	.011
6911 06 19	6	M5x0,8	3	11	2.5	16	.005
6911 08 10	8	G1/8	4.5	13	5	20.5	.011
6911 08 13	8	G1/4	5.5	16	6	19.5	.016
6911 08 17	8	G3/8	5.5	21	6	18	.022
6911 10 13	10	G1/4	5.5	16	7	23	.018
6911 10 17	10	G3/8	5.5	21	8	19.5	.021
6911 10 21	10	G1/2	7	24	8	18	.033
6911 12 17	12	G3/8	5.5	21	9	27	.029
6911 12 21	12	G1/2	7	24	10	22.5	.035
6911 16 17	16	G3/8	7.5	27	9	32.5	.06
6911 16 21	16	G1/2	9	27	12	32.5	.063
6911 16 27	16	G3/4	7.5	32	12	32.5	.096