

Rittal – The System.

Faster – better – everywhere.

► Rail for EMC shielding bracket and strain relief – SZ 2388.650

Date : Apr 26, 2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Rail for EMC shielding bracket and strain relief – SZ 2388.650

created: 26.04.2021 build on www.rittal.com/uk-en



Product description

Design:	C rail to accommodate cable clamps T-head cut-outs on a 40 mm pitch pattern for cable clamping using cable ties
Description:	Combined rail for strain relief and EMC contacting of inserted cables.
Benefits:	Additional contacting on the left or right of the rail via existing holes (9 mm diameter) Prepared for tool-free mounting of EMC shielding brackets
Material:	Extruded aluminium section
Surface finish:	Chromium-free passivated
Supply includes:	1 rail 2 retaining brackets Assembly parts

Product description

To fit:	Enclosure type: VX Enclosure type: TS Width: = 600 mm
Dimensions:	Length: 553 mm
Installation options:	on the horizontal/vertical enclosure section may also be fitted without a retaining bracket on a mounting plate
Packs of:	1 pc(s).

Weight/pack:	0.58 kg
Copper weight (kg per piece):	0
EAN:	4028177698918
Customs tariff number:	73269098
ETIM 7.0:	EC002625
ETIM 6.0:	EC002625
eCl@ss 8.0/8.1:	27189234
eCl@ss 6.0/6.1:	27189214
Product description:	SZ Rail, for EMC rail and stain relief, for W: 600 mm
Approvals	
Certificates:	NA