

Analogue temperature transmitter T91

Analogue temperature transmitter T91

Item number: 39882439

Quantity: 1 pcs.

Order code: T91.10.104-1PF-CELZ

Overview: Analogue temperature transmitter T91
model: T91.10 head mounting, 0...10 VDC
Operating range: B-Head; Ptx, 0,1% Accuracy, 2/3-wire
Input: resistance thermometer Pt100
Output signal: 0...10 VDC, 3-wire
Unit: °C
Measuring range: -50 °C ... +200 °C

Details: Analogue temperature transmitter T91
model: T91.10 head mounting, 0...10 VDC
Operating range: B-Head; Ptx, 0,1% Accuracy, 2/3-wire
Input: resistance thermometer Pt100
Output signal: 0...10 VDC, 3-wire
Unit: °C
Measuring range: -50 °C ... +200 °C

Ready for despatch: 26 working day(s)

Despatch date: 17/05/2023

Pricing: Pricing (EUR):
T91 T04
model T91.10 head mounting, 0...10 VDC: + 68.67
Operating range B-Head; Ptx, 0,1% Accuracy, 2/3-: + 16.58

Subtotal: 85.25
Discount: 20.00 % from Discount of sales discount classes
Net: 68.20

=====

Total: 85.25
Net: 68.20

Sales price: 68.20

Unit price: €68.20

Total: €68.20