

A52.063/1, 0...500°C, 100x8mm

Bimetallic thermometer, for industrial applications A52L

Item number:	45820686
Quantity:	1 pcs.
Order code:	A52.063-1-C1S-BS-C100GDZ-Z-ZZZ TD FZZVC- AZ1ZZZZZZZZZZ
Overview:	A52.063/1, 0...500°C, 100x8mm Process connection: plain, with neck to fit thermowell (thermowell necessary for mounting) Neck: 30 mm flat instrument glass *WIKA*
Details:	Bimetallic thermometer, for industrial applications A52L Specifications according to data sheet: TM 52.01 Accuracy class: class 1 per EN 13190 Case: stainless steel Stem material: stainless steel Model: A52.063, nominal size 63, location of stem centre back Connection design: 1, plain stem Scale range: 0 °C ... 500 °C Process connection: plain, with neck to fit thermowell (thermowell necessary for mounting) Stem diameter: 8 mm Insertion length L1: 100 mm Neck: 30 mm Window: flat instrument glass Case: Stainless steel Ingress protection: IP 43 Manufacturer logo: *WIKA* Stem material: stainless steel