

XY123V-2.54




Dimensions

Poles:	1P-XXP
Pitch:	2.54mm(.100")

Electrical

Standard:	UL	IEC
Voltage Rating:	150	130V
Current Rating:	2A	6A
Wire range:	24-20AWG	0.2-1.0mm ²
Withstanding voltage	AC1250V/Min	



Mechanical

Ambient temperature	-40°C~+105°C
Strip length	10-11mm

Material

Housing:	PA66(UL 94V-0)
Pin header	Brass, Tin Plated
Wire guard	Stainless steel