

<b>Specifications</b>		
Model	UTP1306	UTP1310
Output voltage	0~32V	0~32V
Output current	0~6A	0~10A
Output power	192W	320W
Load regulation	CV<0.1%+5mV CC<0.2%+3mA	
Power regulation	CV<0.01%+5mV CC<0.2%+3mA	
Output regulate resolution	CV: 10mV (typical), CC: 1mA (typical)	
MTBF(e):	≥2000hrs	
Programming accuracy (25°C±5°C)	Voltage	<0.1%+1digit
	Current	<0.2%+3mA
Ripple and noise (20Hz~20MHz)	Voltage	≤10mVrms
	Current	≤5mArms
Display mode	LED voltage and current dual display	
<b>General Characteristics</b>		
Power	Input voltage: 110V AC/220V AC, 50Hz~60Hz	
Display	EBTN LCD	
Product color	White and grey	
Product size (W×H×D)	80mm x 150mm x 230mm	
Product net weight	2kg	2.5kg
Standard quantity per carton	6pcs	
Standard carton size	625mm x 435mm x 300mm	
Standard carton gross weight	12.3kg	16.2kg
<b>Ordering Information</b>		
UTP1300 Series	Switching DC Power Supply (1-Channel, 32V,10A)	UTP1310
	Switching DC Power Supply (1-Channel, 32V, 6A)	UTP1306
Standard Accessories	International standard power cord	/
	Alligator clip test line	/