

Specifications	Range	UT201+	UT202+	UT202A+	UT203+	UT204+
AC current (A)	400A	$\pm(2\%+10)$	$\pm(2\%+10)$		$\pm(2.5\%+5)$	
	600A			$\pm(2\%+10)$		$\pm(2.5\%+5)$
AC current frequency (Hz)	50Hz~100Hz	$\pm(1\%+5)$	$\pm(1\%+5)$	$\pm(1\%+5)$		
DC current (A)	400A				$\pm(2.5\%+5)$	
	600A					$\pm(2.5\%+5)$
AC voltage (V)	600V	$\pm(0.8\%+5)$	$\pm(0.8\%+5)$	$\pm(0.8\%+5)$	$\pm(0.8\%+5)$	$\pm(0.8\%+5)$
AC voltage frequency(Hz)	10Hz~10kHz	$\pm(1\%+5)$	$\pm(1\%+5)$	$\pm(1\%+5)$		
	10Hz~60kHz				$\pm(0.5\%+2)$	$\pm(0.5\%+2)$
DC voltage (A)	600V	$\pm(0.5\%+2)$	$\pm(0.5\%+2)$	$\pm(0.5\%+2)$	$\pm(0.5\%+2)$	$\pm(0.5\%+2)$
Resistance ( $\Omega$ )	40M $\Omega$	$\pm(0.8\%+2)$	$\pm(0.8\%+2)$		$\pm(0.8\%+2)$	
	60M $\Omega$			$\pm(0.8\%+2)$		$\pm(0.8\%+2)$
Capacitance (F)	4mF		$\pm(4\%+5)$			
	40mF				$\pm(4\%+5)$	
	60mF			$\pm(4\%+5)$		$\pm(4\%+5)$
Temperature ( $^{\circ}\text{C}$ )	-40 $^{\circ}\text{C}$ ~1000 $^{\circ}\text{C}$		$\pm(1.5\%+5)$			$\pm(1.5\%+5)$
Frequency (Hz)	10Hz~10MHz			$\pm(0.1\%+4)$	$\pm(0.1\%+4)$	$\pm(0.1\%+4)$
<b>Features</b>						
Display count		4000	4000	6000	4000	6000
Auto range		√	√	√	√	√
Jaw opening		28mm	28mm	28mm	28mm	28mm
True RMS		√	√	√	√	√
NCV		√	√	√	√	√
Live wire test				√		√
Continuity test		√	√	√	√	√
Diode		√	√	√	√	√
MAX/MIN		√	√	√	√	√
Relative mode			√	√	√	√
Zero mode					√	√
Data hold		√	√	√	√	√
Low battery indication		√	√	√	√	√
Auto power off		√	√	√	√	√
<b>General Characteristics</b>						
Power	1.5V battery (R03) x 2					
Display	37mm x 25mm					
Product color	Red and grey					

Product net weight	UT201+/UT202+/UT202A+ : 248g; UT203+/UT204+:235g
Product size	215mm x 63mm x 36mm
Standard accessories	Batteries, test leads, Themocouple (UT202+/UT204+)
Standard individual packing	Gift box, Carring bag, English manual
Standard quantity per carton	40pcs
Standard carton measurement	485mm x 295mm x 385mm
Standard carton gross weight	UT202A+: 17.8kg; UT203+: 16.8kg; UT201+/202+/204+: 17.3kg