

Product Image



/publicpictures/Produktbild/1177320.tif

Master data

Product number:	1177320
EAN:	4007123674541
Artikelverantwortlicher:	Brennenstuhl Tübingen
manufacturer:	Brennenstuhl
Product line:	
Kundenspezifisch:	No
Minimalpflege:	No
Ausleitungskennzeichen:	J
Gewählte Vertriebsregion:	De
Gewählte Sprache:	en

Texts

Is4-Bezeichnung 1/2:

LuxPremium LED Akku CRI Kopflampe SL350AFT, 350lm, CRI96, Fokus,Sensor

Short description for the internet:

Brennenstuhl LuxPremium LED Akku CRI headlamp SL 350 AFT / Head Torch with sensor (headlamp with selectable light colour ideal for detailers, painters and varnishers, IP44, 350lm, up to 40h light duration)

Website-Kurztext:

LuxPremium LED Akku CRI Headlamp SL 350 AFT / Head Torch with sensor and red light (COB-LED, selectable light colour, with maximum colour rendering CRI15= 96, ideal for detailers, painters and varnishers)

Print-Kurztext:

LuxPremium LED Battery CRI Headlamp SL 350 AFT, 350lm, CRI96

Bulletpoint 1:

Super bright detailing headlamp with high quality COB-LED (350lm) thanks to 3-stage changeable light colour 2700K - 4000K - 6500K especially suitable for detailers, painters and varnishers

Bulletpoint 2:

Head Torch with infinitely variable focus and different switching levels, headlight: 100% - 40% -10% - SOS - Red and also with rear light: red, red flashing for even better visibility in the dark

Bulletpoint 3:

Rechargeable LED headlamp with replaceable Li-Ion battery 3.7 V/2.6 Ah with charge indicator and infinitely variable focus from wide-area close-range light to focused long-range light - with up to 40h burn time

Bulletpoint 4:

Thanks to protection class IP44, the headlamp with adjustable tilt angle and lightweight plastic housing is ideal for outdoor use, such as jogging, hiking or assembly work

Bulletpoint 5:

Scope of delivery: 1 x LuxPremium LED Akku CRI headlamp SL 350 AFT (350lm, incl. Li-Ion battery 3,7V/2,6 Ah), 1 x USB charging cable, 1 x forehead plug for changing - in best quality by brennenstuhl®

Online-Beschreibung:

The LuxPremium LED rechargeable CRI headlamp with 350lm by Brennenstuhl is perfect for outdoor use thanks to the IP44 protection rating and is ideal for detailers, painters and varnishers or car workshops. The LED rechargeable head torch has two operating modes (manual and infrared sensor). The super bright headlamp is thanks to the change of different color temperatures and dimming function, suitable for the preparation and assessment of color quality on surfaces and also convinces with the following features:

- * Switch with dimming function 100% / 40% / 10%
- * 3 colour temperatures 2700, 4500, 6500 Kelvin
- * Highest colour rendering CRI 96
- * Light duration up to 40h
- * Stepless focus
- * Exchangeable brow pad
- * Rear light red, red flashing
- * Infrared sensor for contactless switching on and off
- * Battery pack at the back of the head for good balance
- * Stepless focus from wide-area near light to focused far light
- * Exchangeable Li-Ion battery 3.7 V/2.6 Ah with charge indicator
- * USB cable included

Website description:

The LuxPremium LED rechargeable CRI headlamp combines a lightweight and robust plastic housing with a powerful COB LED (350 lumens). Thanks to the IP54 protection class (dust and splash-proof), the headlamp is ideal for detailers, painters and varnishers and car workshops. The change between several colour temperature allows the preparation and assessment of the colour quality on various surfaces, such as when matching colours, and thus offers absolute flexibility through constant working light in the field of vision and free hands for work. The infrared sensor allows the LED head torch to be switched on and off without touching it. Thanks to the switching function (100% - 40% - 10% - SOS - Red), the LED Detaling headlamp has a particularly long burn time of up to 40 hours. The headlamp can be easily recharged via the included USB cable. In addition, the headlamp convinces with the following features:

- * 3 color temperatures 2700, 4500, 6500 Kelvin
- * Highest color rendering CRI 96
- * Stepless focus
- * Exchangeable brow pad
- * Rear light red, red flashing
- * Battery pack at the back of the head for good balance
- * Stepless focus from wide-area near light to focused far light
- * Exchangeable Li-Ion battery 3.7 V/2.6 Ah with charge indicator

Schlagworte:

headlamp brennenstuhl, headlamp brennstuhl, headlamp red light, headlamp red light, headlamp rechargeable, headlamp usb, headlamp back light, headlamp led rechargeable, headlamp waterproof, headlamp led rechargeable, headlamp led usb, headlamp, headlamp led waterproof rechargeable, headlamp head torch, headlam construction site, sensor headlamp, headlamp head torch led, headlamp outdoor, head torch, head torch construction site, sensor head torch, head torch outdoor, head torch backlight, head torch workshop, head torch painter, head torch painter work, headlamp workshop, headlamp painter, headlamp painter work

Subtitle:

Multi-functional with very simple operation.

Print-Beschreibung:

- * With extremely bright COB LED.
- * Switches with colour temperature 2700, 4500 and 6500K especially suitable for detailers, painters and varnishers.
- * Highest colour rendering CRI 96.
- * Two operating modes: manual and infrared sensor.
- * Infrared sensor for contactless switching on.
- * Switch with switching function: 100% - 40% - 10%.
- * Tail light red, flashing red.
- * Stepless focus from wide-area near light to focused far light.
- * Battery pack at the back of the head for good balance.
- * Replaceable Li-Ion battery 3.7 V/2.6 Ah with charge indicator.
- * Adjustable tilt angle, light and robust plastic housing.
- * Replaceable forehead plaster and removable longitudinal strap.

Infotext:

Table article information:

Scope of supply:

Media



/publicpictures/Logo-Brennenstuhl/logo-engineered-in-germany.eps



/publicpictures/lcon/icon-farbspektrum-cri15-96.eps



/publicpictures/lcon/icon-leuchtdauer-40h-max.eps



/publicpictures/lcon/icon-focus-fokus.eps



/publicpictures/lcon/icon-sensor-on-off-hand.eps



/publicpictures/lcon/icon-lumen-350.eps



/publicpictures/Detailansicht/1177320-leuchtkopf-schwenkbar.tif



/publicpictures/Detailansicht/1177320-frontansicht.tif



/publicpictures/Detailansicht/1177320-frontansicht-kaltlicht.tif



/publicpictures/Detailansicht/1177320-frontansicht-kaltlicht-warmlicht.tif



/publicpictures/Detailansicht/1177320-frontansicht-warmlicht.tif



/publicpictures/Detailsicht/1177320-bewegungssensor-wischfunktion-mit-grafik.tif



/publicpictures/Anwendung/1177320-anwendung-kfz-werkstatt-mechaniker-unterboden-4.tif



/publicpictures/Anwendung/1177320-anwendung-kfz-werkstatt-mechaniker-unterboden-9.tif



/publicpictures/Anwendung/1177320-anwendung-kfz-werkstatt-mechaniker-lack-polieren-6.tif



/publicpictures/Anwendung/1177320-anwendung-kfz-werkstatt-mechaniker-innenraum-2.tif

/restrictedpictures/QR-Code/1177320-qr-code-info.eps

Context

Attributkategorie:	Light	Accessories:	
Garantie:	Other (legal)	Ersatzteil:	0293135 1172640061 1172640062
		Similar products:	

Technical data

Batterie		Type of fastening:	Other
Battery type:	18650	Handling:	mobile
Battery technology:	Lithium-ion	Suitable for surface mounting:	No
Rechargeable:	Yes	Suitable for built-in mounting:	No
Replaceable:	Yes	Suitable for ceiling mounting:	No
Number of cells:	1	Suitable for wall mounting:	No
Light duration:	40h	Suitable for suspended mounting:	No

Capacity:	2.6Ah	With mounting bracket:	No
Voltage:	3.7V	With fastening strap:	Yes
IEC indication:	ICR18650	Band closure:	other
Einsatz im Ex-Bereich - ep:	No	Material:	Nylon
Charging time:	5h	Degree of protection (IP):	IP44
Leuchte0Allgemein		Suitable for outdoor area:	Yes
Type of lamp:	Headlamp	Shock resistance:	No
Model:	Other	Watertight:	No
Type of accessories:	other	Min. operation temperature:	-10°C
Housing material:	Plastic	Max. operation temperature:	40°C
Surface finishing:	Matt	Leuchte3Stecksystem	
Halogen free:	Yes	Load input:	Yes
Housing colour:	black	USB-Cable length:	0.6m
Colour cover:	transparent	Leuchtmittel0Allgemein	
Colour:	black	Lamp type:	LED non-replaceable
Lamp type included:	Yes	Packaging:	
Number of lamps:	1	Leuchtmittel1Betriebseigenschaften	
Number of batteries:	1	Life time of light:	50,000h
Battery included:	Yes	Colour rendering index CRI:	90-100 (class 1A)
Rotatable - ep:	No	Colour temperature 1:	6,500K
Collapsible/ Bendable:	Yes	Colour temperature 2:	4,500K
With carrying handle:	No	Colour temperature 3:	2,700K
With turn handle:	No	Adjustable colour temperature:	Levels
Hook rotatable:	No	Colour of light - ep:	965
Integrated magnet:	No	Fluorescent colour:	white
Height adjustable:	No	Multicolour- switch steps:	Yes
Focus:	Yes	Adjustable luminous flux:	Levels
Packaging:		Total luminous flux:	350lm
Luminous range:	28m	Mgv	
Fluorescent colour:	white	Packaging unit (UP):	1
Adjustable colour temperature:	Levels	Weight of product (without packaging):	0.17kg

Adjustable luminous flux:	Levels	Length of product (without packaging):	6cm
Luminous flux:	350lm	Width of product (without packaging):	8.5cm
Luminous flux:	350lm	Height of product (without packaging):	11.5cm
Suitable for emergency lighting:	Yes	Weight of product (including packaging):	0.24kg
Emergency unit integrated:	No	Length of product (including packaging):	6.5cm
With orientation lighting:	No	Width of product (including packaging):	8.9cm
Suitable for accent lighting:	No	Height of product (including packaging):	15cm
Fit for monitor workplace:	No		
Multicolour- switch steps:	No		

Leuchte1elektrWerte

Protection class:	III
Power supply:	Rechargeable battery
Load input for external power supply:	Yes
Max. output current USB:	1A

Leuchte2Anwendung

With light sensor:	Yes
With on/off switch:	Yes
Illuminated switch:	No
With twilight switch:	No

Variantgroup

LuxPremium LED Battery CRI Headlamp SL 350 AFT with colour rendering 15CRI 96

- * With extremely bright COB LED.
- * Switches with colour temperature 2700, 4500 and 6500K especially suitable for detailers, painters and varnishers.
- * Highest colour rendering CRI 96.
- * Two operating modes: manual and infrared sensor.
- * Infrared sensor for contactless switching on.
- * Switch with switching function: 100% - 40% - 10%.
- * Tail light red, flashing red.
- * Stepless focus from wide-area near light to focused far light.
- * Battery pack at the back of the head for good balance.
- * Replaceable Li-Ion battery 3.7 V/2.6 Ah with charge indicator.
- * Adjustable tilt angle, light and robust plastic housing.
- * Replaceable forehead plaster and removable longitudinal strap.

Related Article

1177320



Variant Differentiation