




Type: FBTF1081  
 Product Name: Temperature Fuse 1081



basic parameters:

action temperature °C	action accuracy °C	holding temperature °C	limited temperature °C	rated current A	on-off current A	instantaneous overloading current A
106	101 ± 2	75	165	0.3,0.5,1,2,5,10	1.5I <sub>n</sub>	15I <sub>n</sub>
116	111 ± 2	80	165	0.3,0.5,1,2,5,10	5I <sub>n</sub>	15I <sub>n</sub>
126	121 ± 2	85	165	0.3,0.5,1,2,5,10	1.5I <sub>n</sub>	15I <sub>n</sub>
130	125 ± 2	90	165	0.3,0.5,1,2,5,10	1.5I <sub>n</sub>	15I <sub>n</sub>
136	131 ± 2	95	165	0.3,0.5,1,2,5,10	1.5I <sub>n</sub>	15I <sub>n</sub>
145	140 ± 2	100	165	0.3,0.5,1,2,5,10	1.5I <sub>n</sub>	15I <sub>n</sub>
152	147 ± 2	110	165	0.3,0.5,1,2,5,10	1.5I <sub>n</sub>	15I <sub>n</sub>
170	165 ± 2	120	185	1,2,3,5,10	1.5I <sub>n</sub>	15I <sub>n</sub>

work condition:

1. 工作电压: <250V.	work voltage: <250V
2. 工作频率: 45 - 62Hz.	work frequency: 45 - 62Hz
3. 环境温度: +40℃时达 90% - 95%.	ambient temperature: at +40℃, it can reach 90% - 95%
4. 大气压力: 86 - 106kpa.	atmosphere Pressure: 86 - 106kPa