



Click [here](#) for the 3D model.

General Information

Series	HHBC
Style	Through-Hole
Features	Noise Solution, Switching Power Supply Outlets, DC-DC Converter
RoHS	Yes
Miscellaneous	30 (K) Temperature Rise Max.
Core	Fe-Si

Specifications

Inductance	81 uH
Inductance Tolerance	20%
Current	6 A
Temperature Range	-40/+125°C
DC Resistance	24.7 mOhms

Dimensions

D	30mm MAX
T	15.7mm MAX
LL	9mm +/-3mm
S	11mm NOM
Wire Size	1.2mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	150
Component Weight	26 g