

NOTES:


1. ROHS COMPLIANT
2. MATERIALS:
 FIBER OPTIC: $\varnothing 1.5\text{MM}$ OPTICAL CORE, $\varnothing 2.2\text{MM}$ POLYETHYLENE CABLE JACKET
 LENS MOUNT: OPTICAL GRADE ACRYLIC
 LED MOUNTS: FOR SMD 22 & THR 22 - NYLON 66, UL RATING 94-V2
 FOR THR 5 22 - NYLON 66, UL RATING 94-HB
 LENS: POLYCARBONATE, UL RATING 94-V2
 LENS SPACER: POLYPROPYLENE
3. OPTICAL CORE ENDS POLISHED TO 10 MICRONS
4. PANEL MOUNTING HOLE: $.171" \pm .002$ ($4.34\text{mm} \pm 0.05$) ON $1/4"$ (6.35mm) CENTERS
5. PANEL THICKNESS FOR SML 190: $1/32"$ (0.79mm) TO $1/16"$ (1.60mm);
 SMB 200 AND SMQ 250: $1/16"$ (1.60mm) TO $1/8"$ (3.48mm)
6. FOR ADDED SECURITY FOR SMB 200 AND SMQ 250 USE SPC 040 SPACER
7. FOR BEST RESULTS USE ONLY NARROW VIEWING ANGLE NON-DIFFUSED LEDS WITH OUTPUT POWER GREATER THAN 100mcd
8. U.S. AND FOREIGN PATENTS ISSUED

LITE PIPE ASSEMBLY
 ORDERING CODE (EXAMPLE): **FLX3 XX**


LENGTH	
LENGTH CODE	ACTUAL LENGTH
02	2.0"
04	4.0"
06	6.0"
08	8.0"
12	12.0"
CUSTOM LENGTHS AVAILABLE UPON REQUEST	

REVISIONS					
ECN #	REV.	DESCRIPTION	DATE	INITIALS	CHK'D
-	001	INITIAL RELEASE	2/4/10	KH	AZ
-	002	MOD TO NOTE 4&5: CHG $\varnothing .059$ TO $\varnothing .039$	7/20/10	KH	AZ
-	003	REVISED PER ECR 092810AA01	10/4/10	KH	AZ
397	004	REVISED PER ECR 011812KH01	1/19/12	KH	AZ


MOUNTING OPTIONS (ORDER SEPARATELY)




SMD 22




THR 22




THR 5 22




LENS (ORDER SEPARATELY)




SMB 200



SML 190



SMQ 250

<small>DIMENSION STYLE: INCHES (MM) GENERAL TOLERANCES UNLESS OTHERWISE SPECIFIED:</small> X $\pm .020$ $\pm .508$ XX $\pm .010$ $\pm .254$ XXX $\pm .005$ $\pm .127$ ANGLE $\pm 1^\circ$ <input checked="" type="checkbox"/> SHARP ALL CORNERS AND CHAMF EDGES AS SHOWN THIRD ANGLE PROJECTION <small>PROPRIETARY AND CONFIDENTIAL THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF VISUAL COMMUNICATIONS COMPANY, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF VISUAL COMMUNICATIONS COMPANY, INC IS PROHIBITED.</small>	<small>APPROVAL</small> DRAWN: KHOWARD CHECKED: AZANELLI	<small>DATE</small> 2/4/10 2/10/10	 OPTOELECTRONICS 190 BOSSTICK BLVD, SUITE 101 SAN MARCOS, CA 92069 U.S.A. PHONE: (760) 560-1300, FAX: (760) 560-1301 EMAIL: vccsales@vcc3lite.com	<small>TITLE:</small> 3MM FLEXFIRE FLEXIBLE LITEPIPE		
	<small>MATERIAL</small> SEE NOTES	<small>FINISH</small> SEE NOTES		<small>SCALE:</small> 2:1	<small>SIZE</small> B	<small>DWG. NO.</small> FLX3 XX
<small>DO NOT SCALE DRAWING</small>			SHEET 1 OF 2			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

VCC:

[FLX3 02](#) [FLX3 04](#) [FLX3 06](#) [FLX3 08](#) [FLX3_02](#) [FLX3_04](#) [FLX3_06](#) [FLX3_08](#) [FLX3_12](#)