

Specification Sheet

Part Number: 126-00049



Two piece assembly allows the mount to slide along the strap ensuring proper orientation.

Arrowhead style mount provides low insertion and high extraction force.

Arrowhead disc protects against dirt and other impurities.

1-Pc Cable Tie/Arrowhead Mount w/Wings, 6"L, 50lb, 0.24 - 0.26" Hole Dia, PA66HIRHSUV, Black, 500/bag

Article Number 126-00049

Type T50SSFMM

Color Black (BK)

Quantity Per bag

Product Description Wing design helps stabilize the tie in high vibration applications. One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.

Short Description 1-Pc Cable Tie/Arrowhead Mount w/Wings, 6"L, 50lb, 0.24 - 0.26" Hole Dia, PA66HIRHSUV, Black, 500/bag

Global Part Name

T50SSFm-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)

50.0

Minimum Tensile Strength (Metric)

225.0

Length L (Imperial)

6.3

Length L (Metric)

160.0

Fixation Method

Arrowhead

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.18

Width W (Metric)

4.6

Bundle Diameter Min (Imperial)

0.13

Bundle Diameter Min (Metric)

3.2

Bundle Diameter Max (Imperial)

1.38

Bundle Diameter Max (Metric)

35.0

| | |
|--|--|
| Height H (Imperial) | .20 |
| Height H (Metric) | 5.60 |
| Panel Thickness Min (Imperial) | 0.028 |
| Panel Thickness Max (Imperial) | 0.12 |
| Panel Thickness Min (Metric) | 0.7 |
| Panel Thickness Max (Metric) | 3.0 |
| Mounting Hole Diameter D (Imperial) | 0.24 - 0.26 |
| Mounting Hole Diameter D (Metric) | 6.0 - 6.6 mm |
| Mounting Hole Diameter D Min (Imperial) | 0.24 |
| Mounting Hole Diameter D Max (Imperial) | 0.25 |
| Mounting Hole Diameter D Max (Metric) | 6.6 |
| Material | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| Material Shortcut | PA66HIRHSUV |
| Flammability | UL 94 HB |
| Operating Temperature | -40°F to +221°F (-40°C to +105°C) |

| | |
|-------------------------------------|------------|
| Reach Compliant (Article 33) | Yes |
| ROHS Compliant | Yes |
| Package Quantity (Imperial) | 500 |
| Package Quantity (Metric) | 500 |
| Customs Number | 3926909988 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[126-00049](#)