

DYMO®



LabelManager™ 160 ValuePack



CREATE LABELS FAST WITH SMART KEYS

Just type your text, format it with one-touch smart keys and print!
It's easy to create professional labels in and around the office.


Features

- Large LCD Display
- Computer-style keyboard
- One-touch Smart Keys for fast formatting
- 20+ ways to form text
- 200+ symbols and clip-art images
- Print up to 1/2 in (12mm) wide labels
- Powered by 6xAAA alkaline batteries (not included) or optional adapter



Single Unit Includes:

- LabelManager 160
- 3x D1 Starter Label Cassette, 12mm x 3m Black on White
- Quick Start Guide
- 2 + 1 - Year Limited Warranty*



Quick Specs	
Unit Dimensions (H x W x L)	118 x 203 x 49 mm
Weight (excluding battery)	350 g
Mac®/PC Compatible	No
Accepts Label Sizes	6mm, 9mm and 12mm
Tape Platform	D1, Durables
Resolution	180 dpi
Printing System	Thermal Transfer
Print Speed	12 mm/sec
Barcodes	No
Cutter Type	Manual
Batteries	6 AAA (not included)
Adapter	Yes (optional, sold separately)
Networking	No
Country of Origin	China

Item Number	Description	Length (cm)	Width (cm)	Height (cm)	QTY	EAN	Customer Price
2181011	DY LM 160 QWY BL1 EMEA VP	16,51	6,35	25,4	1	3026981810114	
Accessories (www.dymo.com)							
S0721440	Charging Adapter	11.5	6.0	9.0	1	-	

* +1 year if registered on the Dymo website



100% recycled material used for external cassette



+40% of DYMO® labels are produced* using „Water based solvents“.




DYMO® high quality labels are made in Belgium



D1 Standard Polyester Labels

For hundreds of tasks around the office or home office, such as filing, storage and asset tracking.
Temperature rating: -18°C to 90°C

D1 STANDARD LABELS (7 m)	6 mm	9 mm	12 mm
ABC	S0720780	S0720680	S0720530
ABC	S0720770	S0720670	S0720500
ABC	S0720790	S0720730	S0720580
ABC	-	S0720710	S0720560
ABC	-	S0720740	S0720590
ABC	-	S0720720	S0720570
ABC	-	-	S0720610
ABC	-	S0720690	S0720540
ABC	-	-	S0720510
ABC	-	-	S0720600
ABC	-	S0720700	S0720550
ABC	-	-	S0720520
D1 STANDARD MULTIPACKS (7 m)	6 mm	9 mm	12 mm
ABC	-	2093096	2093097



D1 Durable Vinyl Labels

Industrial strength adhesive helps to ensure labels stay stuck to a variety of surfaces.
Temperature rating: -40°C to 80°C

D1 DURABLE LABELS (3 m)	12 mm
ABC	1978366
ABC	1978365
ABC	1978367
D1 DURABLE LABELS (5.5 m)	12 mm
ABC	1978364



D1 Permanent Polyester Labels

Professional, polished finish ideal for panels, blocks, faceplates, shelves, bins and more.
Temperature rating: -40°C to 150°C*

D1 PERMANENT POLYESTER (5.5 m)	12 mm
ABC	S0718060


*depends on surface



D1 Flexible Nylon Labels

Specifically designed for curved surfaces and wire and cable marking.
Temperature rating: -40°C to 60°C

D1 FLEXIBLE NYLON (3.5 m)	12 mm
ABC	S0718040



The DYMO® high quality labels are made in Belgium



© 2022 Newell Brands

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.

