

Special spirit levels

Marking spirit level Type 70 MAS



Marking out the correct distances for the drill holes while holding the spirit level horizontally or vertically? No problem with STABILA's marking spirit level. Use the sliding markers on the graduation scale to transfer and mark off the distances. Shelf, pictures and anything else that you have to hang can be fitted rapidly and securely.

Light metal rectangular profile, electrostatically coated, with 2 plastic sliding markers and 2 printed centimetre scales. **Measurement accuracy:** in normal position $0.029^\circ = 0.5 \text{ mm/m}$.

Length	80 cm
Art. No.	14111/0



Verticals and horizontals



Marking out rows



Marking – drilling – hanging



Milled measuring surface (up to 120 cm) with 1 horizontal and 2 vertical vials. **Measurement accuracy:** in normal position $0.029^\circ = 0.5 \text{ mm/m}$, overhead measurement $0.043^\circ = 0.75 \text{ mm/m}$.

Length	80 cm	100 cm	122 cm
Art. No.	16403/4	16404/1	16405/8



Bricklayer's spirit level Type 96-2 K

Patented impact protection: Correct discrepancies directly with light taps with the trowel. No tool replacement. The vertical vials in the centre make reading easy. The chamfered vial casing and the special coating are easy to clean.

Type 196-2 K

Also 2 finger grip openings in expensive 2-component technology, for a safe, firm grip when working.



Milled measuring surface (up to 120 cm) with 1 horizontal and 2 vertical vials. **Measurement accuracy:** in normal position $0.029^\circ = 0.5 \text{ mm/m}$, overhead measurement $0.029^\circ = 0.5 \text{ mm/m}$.

Length	122 cm
Art. No.	16406/5

