

PRODUCTS

- Rocker switches
- Pushbutton switches
- Toggle switches
- Slide switches
- Rotary switches
- Foot switches
- Tact and key switches
- Snap-action switches**
- Micro-signal switches
- ECO switches
- Sensors
- Systems and modules
- Accessories
- General information
- Catalog request / download

PRODUCTS ▶ SNAP-ACTION SWITCHES

Snap-action switches

SERIES 1050 - SUBMINIATURE SNAP-ACTION SWITCHES - TO 10 (1.5) A 250 V AC

[◀ Show previous product](#)
[Show next product ▶](#)

1050.6702

[Drawing](#)


Similar to original product

[→ Print data sheet](#)

Product number	1050.6702
Switching function	Changeover switch (SPDT momentary)
Number of poles	1-pole
connections	Quick-connect terminal, 2.8 x 0.5
Mechanical life endurance	1E6
Rating IEC	5 A 250 V AC 5E4
Rating North America	5 A 125 - 250 V AC 1/10 HP
Design	DIN 41635 B
Contact resistance (new condition)	< 100 (1 A 12 V DC) mOhm
Insulation resistance (new condition)	> 100 (500 V DC) MOhm
Proof tracking	175 PTI
Protection type	Connection IP 00
Ambient temperature	-40 °C ... +100 °C
Flammability	UL 94 V-2
Glow wire test temperature	850 °C
Actuators and additional actuators	PA, stainless steel spring steel, L12, lever 2.9 long 3.4 wide with roller diameter 5 of PA gray
Housing description	PBTP
Contact material	Ag
Operating force	≤ 0.6 N
Bounce time	< 5 ms
Difference travel max.	1.0 mm
Free position (FP) max.	20 mm
Operating position (OP)	16.2 ±1.5 mm
Permissible total travel position	13 mm
Approval marks	ENEC 10 / CSA / UL
Shop / Stock version	