


A13-142



FEATURES

- * RATING: 20A max 12V DC or 20A max 24V DC
- * MATERIAL OF SOCKET
 - Housing: nylon with glass fiber (UL 94-HB).
 - Cap: PVC.
- * Mounting plate: nylon with glass fiber (UL 94-HB).
- * Surface mounting case: ABS
- * Watertight sealing cap.
- * SeaLink locking system.
- * LED back light for night time use, available with red, green, blue and white colors. (for A13-142E)
- * Optional accessories – single / dual mounting panel or surface mount case.
- * Refer to A13-194 for the spec. of optional accessories.
- * A13-142E, A13-194 series and A13-196 **unavailable in Australia market.**
- * 10A fits wire 18 AWG.
- * 15A fits wire 16 AWG.
- * 20A fits wire 12 AWG.
- * Fits with ϕ 21 plugs.

Mounting hole



A13-142

SERIES	MOUNTING TYPE	BASE COLOR	DUST COVER COLOR	INPUT RATING
E	P S P:Panel mounting S:Single (Fitting q'ty)	N NONE	N NONE	1 12V
		B BLACK	B BLACK	2 24V
		W WHITE	W WHITE	3 12/24V
21 socket 1 4 4				
12 socket 1 9 4 A	P D P:Panel mounting D:Double (Fitting q'ty)			
1 USB port 1 9 4 B	H S H:Housing mounting S:Single (Fitting q'ty)			
2 USB ports 1 9 6	H D H:Housing mounting D:Double (Fitting q'ty)			
NONE	NONE			

NEW



A13-142E-BB3



A13-142PS-BB3



A13-142HS-BB3



A13-142194BPD-BB3



A13-142194HD-BB3