







GDML 2011 LED 120 YE black	GDML 2011 LED 120 VR YE black	GDML 2011 LED 230 YE black
933 738-212	933 927-212	933 739-212
 <p>function indicator (bipolar LED)</p>	 <p>function indicator (LED) with freewheeling diode and protective circuit (varistor)</p>	 <p>function indicator (bipolar LED)</p>
<p>transparent housing, cable gland grey; Order no. 933 738-712 2 + PE PG 11 (black) max. 1.5 mm2 DIN EN 175 301-803-A transparent A</p>	<p>transparent housing, cable gland grey; Order no. 933 927-712 2 + PE PG 11 (black) max. 1.5 mm2 DIN EN 175 301-803-A transparent A</p>	<p>transparent housing, cable gland grey; Order no. 933 739-712 2 + PE PG 11 (black) max. 1.5 mm2 DIN EN 175 301-803-A transparent A</p>
bipolar LED yellow	LED yellow varistor	bipolar LED yellow
 <p>— connection terminal —C fork type spring</p>	 <p>— connection terminal —C fork type spring</p>	 <p>— connection terminal —C fork type spring</p>
<p>6.3 mm x 0.8 mm, 4.8 mm x 0.8 mm AC/DC 120 V 8 A ≤ 4 mOhm screw 4.5 mm to 11 mm diameter central nut</p>	<p>6.3 mm x 0.8 mm, 4.8 mm x 0.8 mm AC/DC 120 V 8 A ≤ 4 mOhm screw 4.5 mm to 11 mm diameter central nut</p>	<p>6.3 mm x 0.8 mm, 4.8 mm x 0.8 mm AC/DC 250 V 8 A ≤ 4 mOhm screw 4.5 mm to 11 mm diameter central nut</p>
Sn PA PA	Sn PA PA	Sn PA PA
IP 65 (gasket necessary) 3 -40 °C to +90 °C	IP 65 (gasket necessary) 3 -40 °C to +90 °C	IP 65 (gasket necessary) 3 -40 °C to +90 °C
94 HB 94 HB	94 HB 94 HB	94 HB 94 HB
50 pieces	50 pieces	50 pieces
GDM 3-7, Order no. 730 801-002; GDM 3-21, Order no. 731 739-004; GDM 3-16, Order no. 731 531-002; GDM 3011-8, Order no. 732 574-001; GDM 3011 RF-1, Order no. 734 363-001	GDM 3-7, Order no. 730 801-002; GDM 3-21, Order no. 731 739-004; GDM 3-16, Order no. 731 531-002; GDM 3011-8, Order no. 732 574-001; GDM 3011 RF-1, Order no. 734 363-001	GDM 3-7, Order no. 730 801-002; GDM 3-21, Order no. 731 739-004; GDM 3-16, Order no. 731 531-002; GDM 3011-8, Order no. 732 574-001; GDM 3011 RF-1, Order no. 734 363-001