

PRODUCT-DETAILS

AT16/M16/A/BLY

STRAIGHT M16 IP66.69/NC16 BLK/YW



General Information

Extended Product Type	AT16/M16/A/BLY
Product ID	7TCA296170R0105
EAN	5020963037498
Catalog Description	STRAIGHT M16 IP66.69/NC16 BLK/YW
Long Description	Adaptalok ATS, Straight Conduit Fitting, Fixed External Male Thread, Nominal Conduit Size 16mm, M16 Thread, Polyamide (Nylon) 66/TPE, Black with Yellow Elastomer

Additional Information

Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Product Type	Conduit Fitting with Metric Threads

Ordering

EAN	5020963037498
UPC	786210281803
Customs Tariff Number	3917400090

Technical

Number of Batteries	0
Color	Black/Yellow Elastomer
Material	Polyamide/Nylon 6.6

Size NC 16mm

Environmental

WEEE Category Product Not in WEEE Scope

Container Information

Package Level 1 Units	10 piece
Package Level 1 Height	9.84 in 250 mm
Package Level 1 Depth / Length	1 in 25 mm
Package Level 1 Width	7.87 in 200 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	AT16/M16/A/BLY
Instructions and Manuals	AT16/M16/A/BLY
Declaration of Conformity - CE	9AKK107492A9618
RoHS Information	9AKK107992A8994
RoHS Date	9AKK107992A8994
REACH Declaration	9AKK107992A8994

Classifications

ETIM 8	EC001176 - Screw connection for corrugated plastic hose
UNSPSC	39121311

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

