

FUSES & FUSEHOLDERS

5x20mm Glass and Ceramic Fuses




CAM FUSEPLUS Range

5x20mm Quick Blow Glass Fuses

TYPE NO.	RATING	TYPE NO.	RATING
CFB0520F/200	200mA	CFB0520F/3	3A
CFB0520F/250	250mA	CFB0520F/3.15	3.15A
CFB0520F/315	315mA	CFB0520F/4	4A
CFB0520F/400	400mA	CFB0520F/5	5A
CFB0520F/500	500mA	CFB0520F/6.3	6.3A
CFB0520F/630	630mA	CFB0520F/8	8.A
CFB0520F/800	800mA	CFB0520F/10	10A
CFB0520F/1	1A	CFB0520F/12.5	12.5A
CFB0520F/1.25	1.25A	CFB0520F/15	15A
CFB0520F/1.6	1.6A	CFB0520F/16	16A
CFB0520F/2	2A	CFB0520F/20	20A
CFB0520F/2.5	2.5A		

- Quick blow (F) IEC60127
- Excellent I²T characteristics
- Welded element for enhanced vibration tolerance
- Glass cartridge, nickel plated brass end caps
- Colour coded available
- Break capacity 100A/250VAC (250mA-16A)
- RoHs, , , , & approved (315mA-10A)

CFB0520F




5x20mm Time Delay Glass Fuses

TYPE NO.	RATING	TYPE NO.	RATING
CFB0520T/100	100mA	CFB0520T/1.6	1.6A
CFB0520T/125	125mA	CFB0520T/2	2A
CFB0520T/160	160mA	CFB0520T/2.5	2.5A
CFB0520T/200	200mA	CFB0520T/3.15	3.15A
CFB0520T/250	250mA	CFB0520T/4	4A
CFB0520T/315	315mA	CFB0520T/5	5A
CFB0520T/400	400mA	CFB0520T/6.3	6.3A
CFB0520T/500	500mA	CFB0520T/8	8.A
CFB0520T/630	630mA	CFB0520T/10	10A
CFB0520T/800	800mA	CFB0520T/12.5	12.5A
CFB0520T/1	1A		
CFB0520T/1.25	1.25A		

- Time delay (F) IEC60127
- Excellent I²T characteristics
- Welded element for enhanced vibration tolerance
- Glass cartridge, nickel plated end caps-Brass
- RoHs, , , , & approved (500mA - 10A)

CFB0520T




5x20mm Quick Blow Ceramic Fuses

TYPE NO.	RATING	TYPE NO.	RATING
CFB0521CF/500	500mA	CFB0521CF/5	5A
CFB0521CF/630	630mA	CFB0521CF/6.3	6.3A
CFB0521CF/800	800mA	CFB0521CF/7.5	7.5A
CFB0521CF/1	1A	CFB0521CF/8	8.A
CFB0521CF/1.25	1.25A	CFB0521CF/10	10A
CFB0521CF/1.6	1.6A	CFB0521CF/12.5	12.5A
CFB0521CF/2	2A		
CFB0521CF/2.5	2.5A		
CFB0521CF/3.15	3.15A		
CFB0521CF/4	4A		

- Quick blow (F) IEC60127
- Excellent I²T characteristics
- Welded element for enhanced vibration tolerance
- Ceramic cartridge, nickel plated brass end caps
- Sand filled
- RoHs, & approved (500mA-10A)

CFB0521CF




5x20mm Time Delay Ceramic Fuses

TYPE NO.	RATING	TYPE NO.	RATING
CFB0521CT/500	500mA	CFB0521CT/5	5A
CFB0521CT/630	630mA	CFB0521CT/6.3	6.3A
CFB0521CT/800	800mA	CF0521CT/7.5	7.5A
CFB0521CT/1	1A	CFB0521CT/8	8.A
CFB0521CT/1.25	1.25A	CFB0521CT/10	10A
CFB0521CT/1.6	1.6A	CFB0521CT/12.5	12.5A
CFB0521CT/2	2A		
CFB0521CT/2.5	2.5A		
CFB0521CT/3.15	3.15A		
CFB0521CT/4	4A		

- Time delay (T) IEC60127
- Excellent I²T characteristics
- Welded element for enhanced vibration tolerance
- Ceramic cartridge, nickel plated brass end caps
- Sand filled
- , , & approved (200mA - 12.5A)

CFB0521CT



PCB
TERMINAL
BLOCKS

INTER-
CONNECTION

FUSES &
FUSE-
HOLDERS

LEDs &
INDICATORS

MINIATURE
SWITCHES

LIMIT &
SAFETY
SWITCHES

CONTROL
PRODUCTS

INTERFACE
MODULES &
SUPPORTS

RELAY
BASES

DIN RAIL
ENCLOSURES

BATTERIES

SOLAR
PANELS

TRANS-
FORMERS